Model 975XL2SE



Reduced Pressure Principle Assembly with 90° Elbows

Application

Ideal for use where Lead-Free* valves are required. Designed for installation on potable water lines to protect against both backsiphonage and backpressure of contaminated water into the potable water supply. Elbows allow for a very small installation footprint for confined spaces or landscaping. Assembly shall provide protection where a potential health hazard exists.

Standards Compliance

- ASSE® Listed 1013
- IAPMO® Listed
- CSA® Certified
- AWWA compliant C511
- · Approved by the Foundation for Cross Connection Control and Hydraulic Research at the University of Southern California
- Meets the requirements of NSF/ANSI/CAN 61* (SE only)
- *(0.25% MAX. WEIGHTED AVERAGE LEAD CONTENT)

Materials

Main valve body	Low Lead Cast Bronze ASTM B 584
Access covers	Low Lead Cast Bronze ASTM B 584
Fasteners	Stainless Steel, 300 Series
Elastomers	Silicone (FDA Approved)
	Buna Nitrile (FDA Approved)
Polymers	NoryI™
Springs	Stainless Steel, 300 series
Ball valve handles	Stainless steel

Features

Sizes: 3/4", 1", 1-1/4", 1-1/2", 2"	
Maximum working water pressure	175 PSI
Maximum working water temperature	180°F
Hydrostatic test pressure	350 PSI
End connections Threaded	ANSI B1.20.1

Size 3/4"-1" Size 1-1/4"-2" (975XL2SEU) (975XL2SE) NSE/ANSI/CAN 61 LEAD FREE Options (Suffixes can be combined)




- with full port QT ball valves (3/4" -1" standard) -
- with full port QT union ball valves (1 1/4" -2" standard)

Accessories

- Air gap (Model AG)
- Repair kits (rubber only)
- Thermal expansion tank (Mdl. XT)
- Soft seated check valve (Model 40XL2)
- Shock arrester (Model 1250XL)
- QT-SET Quick Test Fitting Set

Relief Valve discharge port:

3/4" - 1"	-	0.63 sq. in				
1 1/4" - 2"	-	1.19	sq.	in.		




Dimensions & Weights (do not include pkg.)

		DIMENSIONS (approximate)															
MOE														F		WE	IGHT
SIZ	Έ	A		В	;	C		D		E		F		UNION I		**⊏	
														VALV	ES		
in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kg
3/4	20	11 5/8	295	2 1/8	54	3	76	3 1/2	89	5	127	5 13/16	148	6 7/8	175	14	6.4
1	25	11 5/8	295	2 1/8	54	3	76	3 1/2	89	5	127	6 5/16	160	7 1/4	184	15	6.8
1 1/4	32	13 5/16	338	2 3/4	70	3 1/2	89	5	127	6 3/4	171	N/A	N/A	6 5/16	160	29	13.2
1 1/2	40	13 1/2	343	2 3/4	70	3 1/2	89	5	127	6 3/4	171	N/A	N/A	7 1/2	191	29	13.2
2	50	14 5/16	364	2 3/4	70	3 1/2	89	5	127	6 3/4	171	N/A	N/A	8 5/8	219	36	16.3

Zurn Industries, LLC | Wilkins 1747 Commerce Way, Paso Robles, CA U.S.A. 93446 Ph. 855-663-9876, Fax 805-238-5766 In Canada | Zurn Industries Limited 7900 Goreway Drive, Unit 10, Brampton, Ontario L6T 5W6, 877-892-5216 www.zurn.com

Rev. F Date: 12/19 Document No. BF-975XL2SE Product No. Model 975XL2SE Patent zurn.com/patents


MODEL 975XL2SE 3/4", 1", 1-1/4", 1-1/2" & 2" (STANDARD & METRIC)



Typical Installation

Local codes shall govern installation requirements. To be installed in accordance with the manufacturers' instructions and the latest edition of the Uniform Plumbing Code. Unless otherwise specified, the assembly shall be mounted at a minimum of 12" (305mm) and a maximum of 30" (762mm) above adequate drains with sufficient side clearance for testing and maintenance. The installation shall be made so that no part of the unit can be submerged.

Capacity thru Schedule 40 Pipe								
Pipe size	5 ft/sec	7.5 ft/sec	10 ft/sec	15 ft/sec				
1/8"	1	1	2	3				
1/4"	2	2	3	5				
3/8"	3	4	6	9				
1/2	5	7	9	14				
3/4"	8	12	17	25				
1"	13	20	27	40				
1 1/4"	23	35	47	70				
1 1/2"	32	48	63	95				
2"	52	78	105	167				



TYPICAL INSTALLATION

DIRECTION OF FLOW

TYPICAL INSTALLATION

Specifications

The Reduced Pressure Principle Backflow Preventer shall be certified to NSF/ANSI/CAN 61 shall be rated to 180°F and fully assembled with 90° street elbows and full port ball valves. The main body, access covers and elbows shall be low lead bronze (ASTM B 584), the seat ring and all internal polymers shall be Noryl[™]. The seat disc elastomers shall be silicone. The first and second check valves shall be accessible for maintenance without removing the relief valve or the entire device from the line. If installed indoors, the installation shall be supplied with an air gap adapter. The Reduced Pressure Principle Backflow Preventer shall be a ZURN WILKINS Model 975XL2SE.