

Features

- Premium construction.
- MasterClean™ spray nozzles prohibit mineral buildup for easy cleaning.
- Intended for use with Rite-Temp® or HiFlow Rite-Temp® valves.
- 2.0 gal/min (7.6 l/min) maximum flow rate showerhead with Katalyst® Spray Technology.

Required Accessories

- K- 2971-KS 3/4" Pressure-balancing Valve
or
K- 11748-K Pressure-Balancing Valve w/Diverter
or
K- 11748-KS Pressure-Balancing Valve w/Diverter
or
K- 304-CS Pressure-balancing Valve With Stops
or
K- 304-CX Pressure-balancing Valve Less Stops
or
K- 304-K Pressure-balancing Valve Less Stops
or
K- 304-KS Pressure-balancing Valve With Stops
or
K- 304-PS Pressure-balancing Valve With Stops
or
K- 304-PX Pressure-balancing Valve Less Steps
or
K- 304-US Pressure-balancing Valve With Stops
or
K- 304-UX Pressure-balancing Valve Less Stops

Recommended Accessories

- 88526 Thin Wall Trim Kit
1016453 Diverter Button Kit
1073881 Deep Rough-in Kit
1092535 Roughing-in Kit
1156950 Roughing-in Kit




Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
EPA WaterSense®

KOHLER® Lifetime Limited Warranty for Cast Iron Components

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Showerhead:

Rated maximum flow: 2 gal/min (7.6 l/min)

Pressure: 80 psi (5.5 bar)

Notes

For use with automatic compensating valves rated at 1.7 gal/min (6.4 l/min) or less.

Install this product according to the installation guide.

NOTICE: Risk of product damage. Long screws, for installing trim, can damage the K-2971-KS valve. Consult the trim installation guide to verify if the thin wall installation kit (88526) is needed.

Install straight pipe or tube drop of 7" (178 mm) to 18" (457 mm) with single elbow between valve and wall-mount spout.