

# High-Efficiency GreenSpec® Listed Single Filtered Water Cooler Models LZSG8

### RATED FOR INDOOR USE ONLY

#### **PRODUCT SPECIFICATION**

High-efficiency electric, refrigerated water cooler. Model LZSG8 shall deliver 8 GPH of 50° F drinking water at 90° F ambient and 80° F inlet water. Unit shall meet ADA guidelines. Shall include the WaterSentry<sup>®</sup> VII 1500-gallon capacity filter, certified to NSF/ANSI 42 and 53. Unit shall be lead-free design which is certified to NSF/ANSI 61 and 372 and meets Federal and State low-lead requirements. Unit shall be certified to UL399 and CAN/CSA 22.2 No. 120. Unit shall be GreenSpec® Listed.

#### STANDARD FEATURES

- Energy efficiency performance exceeds average market performance by 35%
- W aterSentry<sup>®</sup> VII 1500-gallon capacity Filtration System, certified to NSF/ANSI 42 & 53 (Lead, Class 1 Particulate, Chlorine, Taste & Odor)
- · Easy-touch front and side pushbar controls
- F lexi-Guard<sup>®</sup> StreamSaver<sup>™</sup> water conservation bubbler
- · Cooler panel finishes: Light Gray Granite or Stainless Steel

#### **COOLING SYSTEM**

- High-efficiency Compressor: hermetically-sealed, reciprocating type, single phase. Sealed-in lifetime lubrication.
- Condenser: Fan cooled, copper tube with aluminum fins. Fan motor is permanently lubricated.
- Cooling Unit: Combination tube-tank type. Self-cleansing. Continuous copper tubing with stainless steel tank. Fully insulated with EPS foam which meets UL requirements for self-extinguishing material.
- Refrigerant Control: Refrigerant R134a is controlled by accurately calibrated capillary tube.
- Temperature Control: Easily accessible enclosed adjustable thermostat is factory preset. Requires no adjustment other than for altitude requirements,

#### **CAPACITIES CHART**

Model	Voltage / Hertz	Chilling** Capacity	F.L. Amps	Rated Watts	Approx. Ship Wt.
LZSG8*	115V / 60Hz	8 GPH	3.2	360	68

\*Color code of (L) Light Gray Granite or (S) Stainless Steel cooler panels \*\*Based on 80°F inlet water & 90°F ambient air temp for 50°F chilled drinking water.



### **CONSTRUCTION**

- Stainless Steel basin with integral drain
- Galvanized structural steel cooler chassis
  provides structural integrity
- Cooler cabinet available as Light Gray Granite Vinyl Clad Steel or Stainless Steel (additional cost) construction.
- F lexi-Guard<sup>®</sup> StreamSaver<sup>™</sup> Safety Bubbler utilizes an infused anti-microbial pliable polyester elastomer to prevent accidental mouth injuries. Flexes on impact. Lower-flow waterefficient water stream.

#### Replacement Filter: 51299C

**Warranty**: 5 year limited warranty on the unit's refrigeration system. Electrical components and water system are warranted for 12 months from date of installation or 18 months from factory shipment, whichever date falls first.

#### **CERTIFICATIONS / STANDARDS**

- ADA Compliant
- UL399 and CAN/CSA 22.2 No. 120 Certified
- ANSI/NSF 61 and 372 Certified
- ANSI/NSF 42 and 53 Certified (Filter only)
- GreenSp ec<sup>®</sup> Listed



This specification describes an Elkay product with design, quality and functional benefits to the user. When making a comparison of other producer's offerings, be certain these features are not overlooked.

In keeping with our policy of continuing product improvement, Elkay reserves the right to change specifications without notice. Please visit elkayusa.com for the most current version. 2222 Camden Court Oak Brook, IL 60523 630-572-3192 Elkayusa.com

# High-Efficiency, GreenSpec<sup>®</sup>Listed Single Filtered Water Cooler **Models LZSG8**

# **IMPORTANT! INSTALLER PLEASE NOTE:**

These units are designed and built to provide water to the user which has not been altered by materials in the cooler waterway. The grounding of electrical equipment such as telephone, computers, etc. to water lines is a common procedure. This grounding may be in the building but may also occur away from the building. This grounding can cause electrical feedback into a water cooler creating an electrolysis which results in a metallic taste or an increase in the metal content of the water. This condition is avoidable by installing the cooler using the proper materials as shown.

# NOTICE

9/32" O HOLES (6)

В Ε

D

F

17 7/16"

443mm

7mm

21 7/8"

556mm

19'

483mm

This water cooler must be connected to the water supply using a dielectric coupling. The cooler is furnished with a nonmetallic strainer which meets this requirement. The drain trap which is provided by the installer should also be plastic to completely isolate the cooler from the building plumbing system

6 3/8"

162mm


18 3/8" 467mm

6 3/8"

162mm



\*Rated for indoor use only



## LEGEND:

A = Recommended Water Supply location. Shut-off Valve (not furnished) to accept 3/8 O.D. unplated copper tube. 3" (76mm) maximum out from wall.

178mm

2 51mm

3 7/8" 98mm

5 3/4"

146mm

178mm

354mm

- B = Recommended Waste Outlet location. To accommodate 1-1/4" nominal drain. Drain stub 2" out from wall.
- C = 1-1/4" Trap (not furnished)
- D = Electrical Supply (3) Wire Recessed Box Duplex Outlet.
- E = Insure proper ventilation by maintaining 6" (152mm) minimum clearance from cabinet louvers to wall.
- F = 7/16" Bolt Holes for fastening to wall.
- \*\*NEW INSTALLATIONS MUST USE GROUND FAULT CIRCUIT INTERRUPTER (GFCI)

FINISHED FLOOR

Job Name:					
Date:	Qty:				
Contact Info (Name, Phone, Email):					
Approval:					

12 1/2'

318mm