


# S-AG 38 Series SITE SIZABLE PVC

- S-AG 3836 36" Complete Kit
- S-AG 3848 48" Complete Kit
- S-AG 3860 60" Complete Kit
- S-AG 3872 72" Complete Kit
- S-AG 3896 96" Complete Kit

### **Features**

- Modify length and outlet location on site
- Indoor or outdoor use
- PVC Channel
- 12 gauge, 316L stainless steel Wedge Wire grate
- Works with 2" clamp down floor with 2" throat/strainer size (not included)
- NOT INTENDED for installation across a barrier-free threshold
- Compatible with: PVC Liner, Rubber Liner (Chloraloy ®), Hot Mop, Lead Pan, Copper Pan, or Fiberglass
- Flow rate 9 gpm per outlet
  - Flow rate measured at outlet only. Measurement does not account for water in channel or sheeting on shower floor.
  - Additional outlets can be added and combined into a larger waste line to increase flow rates




### Care & Maintenance

S-AG 38 stainless steel linear drain top grates are made of 316L stainless steel. This material is non-porous, hygienic, rust-free and extremely durable. Bar Keepers Friend® and Soft Scrub® are commonly available products that can be used to protect and clean your Satin Stainless drain cover. For stains that have been left for an excessive amount of time, stronger cleaning agents such as Compound 302® may be needed. For Polished Stainless and other finishes we recommend a mild soap and a soft cloth for cleaning. DO NOT use any abrasive cleaners, scrub pads or allow household cleaning agents, such as bleach, to sit on the drain cover for a long period of time. Stainless steel does not rust. External factors, such as contamination from other highly ferrous metals, built up road salt, sea salt, or chlorine may have caused "surface" rust which can be removed using Barkeepers Friend®, Soft Scrub® with Bleach, or Compound 302®. Always follow the directions on the bottle. Follow proper maintenance procedures to prevent excessive surface rust. In areas of frequent exposure to salt, chlorine, and other chemical compounds, maintenance of the stainless grates should be performed at least 2-3 times per year.

Infinity Drain 145 Dixon Avnue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.lnfinitydrain.com








Model Number	Complete Kit Contents	A (Maximum Overall Length)	B (Maximum Grate Length)
S-AG 3836	1 - A 3836 Stainless Steel Grate 1 - G 3836 PVC Channel 2 - E 38 PVC Stop End 1 - S 32 PVC Outlet Section 1 - S 50 PVC Threaded Outlet 1 - HS 2 2" Hair Strainer 2 - CT 36 Channel Trim 1- AKEY Lift Out Key	36"	35 7/8"
S-AG 3848	1 - A 3848 Stainless Steel Grate 1 - G 3848 PVC Channel 2 - E 38 PVC Stop End 1 - S 32 PVC Outlet Section 1 - S 50 PVC Threaded Outlet 1 - HS 2 2" Hair Strainer 2 - CT 48 Channel Trim 1 - AKEY Lift Out Key	48"	47 7/8″
S-AG 3860	1 - A 3860 Stainless Steel Grate 1 - G 3860 PVC Channel 2 - E 38 PVC Stop End 1 - S 32 PVC Outlet Section 1 - S 50 PVC Threaded Outlet 1 - HS 2 2" Hair Strainer 2 - CT 60 Channel Trim 1 - AKEY Lift Out Key	60"	59 7/8"


Finishes					
□ Satin Stainless	Polished Stainless	□ Oil Rubbed Bronze	□ Satin Bronze	□ Matte Black	

Infinity Drain 145 Dixon Avnue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.Infinitydrain.com









Model Number	Complete Kit Contents	A (Maximum Overall Length)	B (Maximum Grate Length)
S-AG 3896	2 - A 3848 Stainless Steel Grate 1 - G 3896 PVC Channel 2 - E 38 PVC Stop End 2 - S 32 PVC Outlet Section 2 - S 50 PVC Threaded Outlet 2 - HS 2 2" Hair Strainer 2 - CT 96 Channel Trim 1 - AKEY Lift Out Key	96"	47 7/8" (x 2)

Finishes					
□ Satin Stainless	□ Polished Stainless	□ Oil Rubbed Bronze	□ Satin Bronze	□ Matte Black	

Infinity Drain 145 Dixon Avnue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.lnfinitydrain.com





### ADDITIONAL INFORMATION

### Threshold Installation

For threshold installs, we recommend the drain run exactly wall-to-wall to block any water from leaving the shower or wet area. We do not recommend thinner or tile-in type drains for threshold installations due to the lack of channel width needed to sufficiently catch the water.

Site Sizable models that are NOT recommended for Threshold Installation include:

S-AG 38, S-DG 38, S-TIFAS 65, S-TIF 65, S-TIFAS 99

#### Wall to Wall Installation

One way to ensure proper drainage is to install the linear drain from wall-to-wall. The Site Sizeable (S) Series is a flexible solution, which allows for "site sizing" the length of the drain by cutting the grate and channel to the exact finished wall- to-wall dimension. Infinity Drain's FX, FF, & FT series can be custom fabricated for the exact desired length and outlet location.

### Against a Wall Installation

The (S) Site Sizeable and Fixed (FX) Series require a traditional clamping drain body for PVC Liner, Chloroloy, Lead Pan, Copper, Fiberglass, and Hot Mop type waterproofing. The diameter of the clamp down drain body creates a challenge for flush against the wall installations.

To properly achieve against the wall installations, it is recommended to build out the back wall with a double layer of wall board.

### Outlets

Site sizable products can be used in both indoor and outdoor applications. For indoor installations, we recommend one outlet for every 60" of drain. Our 72", 80", and 96" kits come standard with two outlet assemblies. Site Sizeable (S) Series can add additional outlet components to the kit. Outdoor installations: Outlet frequency is dependent on drain application and geographic location. Please contact us with questions regarding your specific installation.

Infinity Drain's Site Sizable (S) linear drains can be joined together to create infinite lengths for outdoor and indoor applications. We offer threaded and non-threaded outlets, 90° angle joiners, straight joiners, and custom fabrication.

Optional Components			
F 65	PVC Non-Threaded Outlet		
GJC 38	PVC Straight Joiner Strip		
GAM 38	PVC 90° Angle Joiner		
TNRN-P	PVC Threaded Extension Nipple		
UCP 2	Universal 2" Clamping Plate		
UCP 4	Universal 4" Clamping Plate		
UCP 42 Universal Reducing Plate (Adapts 4" or 3" existing throat size to 2")			
Add Clamp Down Drain			
CDA 22 Clamp Down Drain ABS			
CDI 22	Clamp Down Drain Cast Iron		
CDP 22 Clamp Down Drain PVC			

Available components for longer lengths				
A 3836	36" Stainless Steel Grate	G 38108	108" PVC Channel	
A 3848	48" Stainless Steel Grate	E 38	PVC Stop End	
A 3860	60" Stainless Steel Grate	S 32	PVC Outlet Section	
A 3872	72" Stainless Steel Grate	S 50	PVC Threaded Nipple	
G 3836	36" PVC Channel	CT 36	36" Channel Trim	
G 3848	48" PVC Channel	CT 48	48" Channel Trim	
G 3860	60" PVC Channel	CT 60	60" Channel Trim	
G 3872	72" PVC Channel	CT 72	72" Channel Trim	
G 3896	96" PVC Channel	NOTE: For indoor applications and outdoor applications where exposure to users without footwear is possible Channel trim (CT) is not recommended on drains over 96" or drains with configurations that include turns.  The installation of channel trim on site sizable linear drains that fall within the outlined conditions listed are at the judgement of the installer, independent of Infinity Drain, LTD.		

Infinity Drain 145 Dixon Avnue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.Infinitydrain.com



