



GENERAL PRODUCT SPECIFICATION

Item No.	MRO100
-----------------	---------------

Date	6-26-03	Replaces	4-2-03	No. Pages	1
-------------	---------	-----------------	--------	------------------	---

Product Description:

Style	Pads ; perforated on centerline for dividing in half for smaller applications
Item Size (each)	16" x 20"
Color	Gray
Composition	100% Polypropylene
Structure	A nonwoven mat of randomly oriented Micro-fibers [2-10 micron diameters]
Technology	Meltblown, 3-ply
Absorbency	Universal (Hydrophilic + Oleophilic)
Bonding	Bonded (staggered pattern) + Mechanical entanglement

Intended Application	Low -Lint Chemical Resistant Sorbent for Water, Oil, or Solvent Base Liquids
-----------------------------	--

Absorbency Capacity	29 gal. per bale (saturated; medium viscosity-12.5x)
----------------------------	--

Packaging Description:

Package configuration	1-Case	Pkg. Weight	19.5-lbs (16)
Items per Package	100-Pads/Case	Pkg. Dimensions	17"x20.5"x15.5"H
Container type	Carton		

Physical Properties:

<u>Parameter</u>	<u>SPC Test Method</u>	<u>Units</u>	<u>Nominal</u>	<u>(+/-)Tolerance</u>
Basis Weight	SPCTM-002A	G/M2	370	37
Caliper	SPCTM-003A	mils	195	20
Absorbency** (med. Oil)	SPCTM-004B	gL/gS	12.5	2
Tensile Strength	SPCTM-006	lbs	18	2
Color	Visual	-----	Gray	per standard

The above properties are "nominal" values used for **PROCESS CONTROL** when the product is produced and/or inspected. Performance "nominals" may vary depending upon the specific application, and/or the environment being applied, stored, or shipped.

** The "Absorbency" Spec and "SPCTM004" test method is based on the protocol of ASTM F726, using SAE20 non-detergent as the Oil Type, medium viscosity.

Attributes	Product will be free of foreign material contamination, rips, holes, and tears.
Labeling	Each package to be clearly labeled with Company Name, Address, Item No., Date, and/or Package Code (Bar Code).
Certification	Make no changes in basic process or composition without notifying customer. Claims for non-conformance of goods must be made within 60-days of delivery.