

SUPER SINGLE® Pump Switch

Mercury activated, wide-angle switch designed to control pumps up to 1 HP at 120 VAC and 2 HP at 230 VAC.

This mercury activated, wide-angle pump switch provides automatic control of pumps in non-potable water and sewage applications. This switch is not sensitive to rotation or turbulence.

The **Super Single®** pump switch is suitable for use with intrinsically safe circuits. Contact SJE-Rhombus regarding specific intrinsically safe applications.





U.S. Patent No. 4,302,641

FEATURES

- Patented tumbler assembly gives positive pump on or pump off.
- Controls pumps up to 1 HP at 120 VAC and 2 HP at 230 VAC.
- Adjustable pumping range of 6.5 to 13.5 inches (176.5 to 34 cm).
- Includes standard mounting clamp and boxed packaging.
- UL Recognized for use in non-potable water and sewage.
- CSA Certified.
- Three-year limited warranty.



Member of
Hydraulic
Pump Switches



OPTIONS

This switch is available:

- for pump down or pump up applications as specified by part number.
- with a 120 VAC or 230 VAC piggy-back plug.
- without a plug for direct wiring in 120 VAC or 230 VAC applications.
- in standard cable lengths of 10, 15, 20, or 30 feet and 3, 5, 6, or 10 meters (longer lengths available).

SPECIFICATIONS

CABLE: flexible 14 gauge, 2 conductor (UL, CSA) SJOW, water-resistant (CPE)

FLOAT: 3.38 inch diameter x 4.25 inch long (8.58 x 10.80 cm) high impact, corrosion resistant, PVC housing for use in sewage and non-potable water up to 140°F (60°C)

MERCURY SWITCH: mercury-to-mercury contacts, hermetically sealed in a steel capsule

ELECTRICAL:

120 VAC 50/60Hz Single Phase:

Maximum Pump Running Current:

15 amps

Maximum Pump Starting Current:

55 amps

Recommended Pump HP:

1 HP or less

230 VAC 50/60Hz Single Phase:

Maximum Pump Running Current:

12 amps

Maximum Pump Starting Current:

35 amps

Pump HP:

2 HP or less

NOTE: This switch must be used with pumps that provide integral thermal overload protection.

PUMP SWITCHES
(MERCURY)

**SJE
Rhombus®**

PO Box 1708, Detroit Lakes, MN 56502

1-888-DIAL-SJE • 1-218-847-1317

1-218-847-4617 Fax

email: sje@sjerhombus.com

www.sjerhombus.com

SEE BACKSIDE FOR ORDERING INFORMATION.

SUPER SINGLE® Pump Switch

Mercury activated, wide-angle switch designed to control pumps up to 1 HP at 120 VAC and 2 HP at 230 VAC.

ORDERING INFORMATION

PUMP DOWN ↓		PUMP UP ↑		List Price	Shipping Weight
Part #	Description	Part #	Description		
1001958	10SSD1WP	1001965	10SSU1WP	\$109.80	1.75 lbs.
1001961	10SSD2WP	1001967	10SSU2WP	\$112.11	1.76 lbs.
1001963	10SSDWOP	1001969	10SSUWOP	\$102.19	1.65 lbs.
1001971	15SSD1WP	1001977	15SSU1WP	\$113.53	2.15 lbs.
1001973	15SSD2WP	1001979	15SSU2WP	\$115.68	2.18 lbs.
1001975	15SSDWOP	1001981	15SSUWOP	\$105.78	2.08 lbs.
1001983	20SSD1WP	1001989	20SSU1WP	\$116.99	2.67 lbs.
1001985	20SSD2WP	1001991	20SSU2WP	\$119.13	2.71 lbs.
1001987	20SSDWOP	1001993	20SSUWOP	\$109.23	2.59 lbs.
1001988	30SSD1WP	1002000	30SSU1WP	\$125.01	3.35 lbs.
1001996	30SSD2WP	1002002	30SSU2WP	\$127.31	3.39 lbs.
1001998	30SSDWOP	1002004	30SSUWOP	\$117.41	3.27 lbs.

D = Pump Down U = Pump Up 1 = 120 VAC 2 = 230 VAC

WP = With Plug WOP = With Out Plug

NOTE: Descriptions are grouped by cable length measured in feet (10, 15, 20, 30).

OPTIONS

MOUNTING CLAMP

is standard.
If mounting clamp is not required, specify and deduct 60¢ from list price.

CABLE WEIGHT MOUNTING

Is also available.

PACKAGING

Boxed - Standard

Bagged - Specify and deduct 40¢ from list price.

Bulk - Specify and deduct 60¢ from list price.

ADDITIONAL CABLE

Additional cable length over 30 feet is available at \$1.60 per foot (list price).

UL Recognized for Water & Sewage



SPECIFICATIONS

PUMPING RANGE: 6.5 to 13.5 inches (16.5 cm to 34 cm)

CABLE: flexible 14 gauge, 2 conductor (UL, CSA) SJOW, water-resistant (CPE)

FLOAT: 3.38 inch diameter x 4.25 inch long (8.58 cm x 10.80 cm), high impact, corrosion resistant, PVC housing for use in sewage and non-potable water up to 140°F (60°C)

MERCURY SWITCH: mercury-to-mercury contacts, hermetically sealed in a steel capsule

ELECTRICAL:

Voltage 50Hz/60Hz Single Phase	Max. Pump Run Current	Max. Pump Start Current	Recommended Pump HP
120 VAC	15 amps	55 amps	1 HP or less
230 VAC	12 amps	35 amps	2 HP or less

NOTE: This switch must be used with pumps that provide integral thermal overload protection. Suitable for use with intrinsically safe circuits.

Contact SJE-Rhombus regarding specific intrinsically safe applications.

OTHER INFORMATION

PUMP DOWN is normally open contacts for emptying.

PUMP UP is normally closed contacts for filling.

DIRECT WIRING

Units used for direct wiring (without plug) may be used in either 120 VAC or 230 VAC applications within specified amp ratings.



www.sjrhombus.com
sje@sjrhombus.com

Cat Page PN 1012514M
© SJE-Rhombus 02/13

Call or fax your order!

1-888-DIAL-SJE (1-888-342-5753) / Fax 218-847-4617