

### Features

- Plastic construction.
- Intended for use with Rite-Temp® or HiFlow Rite-Temp® valves.
- Includes showerhead with arm and flange, and faceplate with handle.
- 2.0 gal/min (7.6 l/min) maximum flow rate showerhead with Katalyst® Spray Technology.

### Required Accessories

- K- 2971-KS 3/4" Pressure-balancing Valve  
or  
K- 304-CS Pressure-balancing Valve With Stops  
or  
K- 304-CX Pressure-balancing Valve Less Stops  
or  
K- 304-K Pressure-balancing Valve Less Stops  
or  
K- 304-KS Pressure-balancing Valve With Stops  
or  
K- 304-PS Pressure-balancing Valve With Stops  
or  
K- 304-PX Pressure-balancing Valve Less Steps  
or  
K- 304-US Pressure-balancing Valve With Stops  
or  
K- 304-UX Pressure-balancing Valve Less Stops

### Optional Accessories

- 1073881 Deep Rough-in Kit  
88526 Thin Wall Trim Kit




### Codes/Standards

ASME A112.18.1/CSA B125.1  
ASSE 1016/ASME A112.1016/CSA B125.16  
DOE - Energy Policy Act 1992  
EPA WaterSense®

### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Showerhead:

Rated maximum flow: 2 gal/min (7.6 l/min)

Pressure: 80 psi (5.5 bar)

### Notes

For use with automatic compensating valves rated at 1.7 gal/min (6.4 l/min) or less.

Install this product according to the installation guide.

**NOTICE:** Risk of product damage. Long screws, for installing trim, can damage the K-2971-KS valve. Consult the trim installation guide to verify if the thin wall installation kit (88526) is needed.

Avoid cross-flow conditions. Do not install shut-off device on either valve outlet.

Install straight pipe or tube drop of 7" (178 mm) to 18" (457 mm) with single elbow between valve and wall-mount spout.