



Profi™/MC

Floor Cleaner/Oil &
Grease Remover



Nonionic oil and grease remover for all resilient and synthetic rubber flooring. An integral part of a comprehensive floor care program for cleaning, stripping and sealing rubber floors.

Effective

- Emulsifies dirt quickly
- Neutral pH and butyl-free

Versatile

- Gentle enough to use on resilient or rubber flooring
 - Safe for use on most washable surfaces
-

Use Directions

- Position wet floor signs around area to be cleaned.
- Depending upon soil level, dilute product according to directions below with warm water.
- Distribute solution and allow to soak for 5-10 minutes (as conditions require) before scrubbing.
- Mop up or wet vacuum slurry.

Note: When cleaning cold floors, use hot water for best results (up to 140° F).

Note: Floors will be slippery when wet or contaminated with foreign materials. Promptly clean up spills and foreign materials.

Dilution for Concrete and Resilient Rubber Studded Flooring

- Light Soil Level: 1-2 oz. / gallon
- Heavy Soil Level: 3-4 oz. / gallon



Dilution for Studded Rubber Flooring

- Stripping of Silicone & Paraffin: 4 oz. / gallon
- Cleaning: 1-2 oz. / gallon

Product Specifications

Description	
Color/Form	Opaque white liquid
Flash Point	> 200° F (> 93.4° C)
pH	8.8 (Concentrate) 8.3 (Use Dilution 1:32)
Scent	Surfactant
Shelf Life	2 years
Solubility	Dispersible
Specific Gravity	1.0

Available Items

Product Code		Description/Package Size	Dilution
94512759		4 x 1 gallon / 3.78 L Containers	1:32-1:128
4512759			

Safety Reminder

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use, and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDSs are available on-line at www.sealedair.com or by calling 888 352 2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate. Please refer to the Diversey HazMat Library, only available through Internet Explorer, <http://naextranet.diversey.com/dot/>, for up to date shipping information.