

PF3001LS

ACCUFIT Pressure Balance Tub and Shower Stops



Product Features

- Pressure balance valve less stops
- One-piece cartridge design for ease of maintenance
- Ceramic disc valve cartridge
- Back-to-back capability
- Forged brass valve body
- Optional air test cap available
- Adjustable temperature limit stop
- 6.3 GPM flow rate at 60 psi
- IAPMO Approved
- Quick remove plaster guard
- Easy mounting brackets
- Meets or exceeds ASSE 1016-P standards (anti-scald)



PF3001LS

Model Numbers


- PF3001LS** Ceramic disc tub & shower valve without stops MIP & SWT
- PF3001CLS** Ceramic disc tub & shower valve without stops CPVC connection
- PF3001FLS** Ceramic disc tub & shower valve without stops FIP
- PF3001PLS** Ceramic disc tub & shower valve without stops PEX ASTM F1807 crimp connector

Parts Available

- ACF3001LSCRT** Replacement cartridge assembly
- ACF3001AIR** Air test cap
- ACF3001GRD** Plaster guard
- ACF3001EXTCP** Deep rough extension kit CP
- ACF3001EXTBN** Deep rough extension kit BN
- ACF3001EXTORB** Deep rough extension kit ORB

	A (in)	A (mm)
PF3001LS	3-1/4	83
PF3001CLS	6-1/4	158
PF3001FLS	3-1/8	80
PF3001PLS	4-3/8	110

Product Specifications



Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO faucet carries a limited lifetime warranty when installed in residential applications. The warranty is five years in commercial applications. This product meets ANSI: A112.18.1M and ASSE 1016-P

