THIS SPACE FOR DESIGNER/ENGINEER APPROVAL				
Job/Customer	Date	Contractor		
Model Specified	Qty	Approved By		
Designer/Engineer	Date	Contractor's PO#		
Submitted by	Date	Other		

D

1370 Series

Double Flanged Check

Forged Brass Check Valve w/ Rotating Flange

CASE

Α

Includes One Set of Mounting Bolts & Full-Faced Flange Gasket

Flange x Rotating Flange

150 PSI @ 200°F

SIZE

CTN

ISO 9001

ITEM #

			Cracking	Recommended	

G

Cv

Pressure

(PSI)

0.23

0.17


Flow Range

(GPM)

15-50

55-120


The **ISOLATOR**




В



NO.	DESCRIPTION	MATERIAL
1	FLANGE BODY	BRASS
2	CHECK VALVE BODY	ABS
3	O-RING INNER SEAL	NBR
4	SPRING	STAINLESS STEEL
5	POPPET	ABS
6	O-RING OUTER SEAL	NBR
7	RETAINING RING	STAINLESS STEEL
8	ROTATING FLANGE	BRASS
9	ROTATING FLANGE RING	STAINLESS STEEL
10	FLANGE NUTS & BOLTS	STEEL ZP





TEMP °F	PSI
100	150
150	150
200	150
250	N/A
300	N/A
350	N/A
366	N/A

Specifications: Designed for residential, commercial or industrial use with water or a glycol in conjunction with a Webstone Isolator Uni-Flange Ball Valve on circulator pumps without integral checks. The valve operates in a horizontal or vertical position. The valve must be installed so that the directional arrow on the body corresponds with the system flow. The rotating flange is secured by a snug-fit snap-ring that provides greater control over positioning during installation.

Quality and Commitment Since 1954