XLTH Outdoor Units 18, 24,000 BTUs

AOU18RLXFZH, AOU24RLXFZH






AOU



Ambient Heating Temperature of -15°F

Other models may go as low as -5°F, however they do not include a base heater and other advancements found in XLTH models.

> The base of Fujitsu's XLTH outdoor condensing units.




When temperatures reach 36°F, a built-in heater warms the base of the outdoor unit so that condensation doesn't Base Drainage Holes freeze. Without a heater, freezing condensate can cause noise, damage to the fan blade, condenser, and system performance.

The cultivated base design discharges melted water through many holes located at the bottom of the unit.

Improved Heating Capacity

Heating capacity at low outdoor temperatures was improved by adopting a large heat exchanger and a high capacity compressor.



Connectable Indoor Unit Number
Connectable Unit Capacity Class BTU/h
Rated Capacity Cooling/Heating BTU/h
Clg. Operating Range °F(°C)

Htg. Operating Range °F(°C) Input Power: Clg/Htg Rated kW* Voltage/Frequency/Phase

Current: Total Max. (A) Minimum Circuit Ampacity (A) MAX.CRT.BKR (A) Outdoor Fan Airflow CFM (Clg/Htg) Fan: Type x Quantity

Sound Pressure Level Cooling dB(A) Sound Pressure Level Heating dB(A) Pre-Charge Length Total Ft (m) Max. Length Total Ft (m) Max. Length Each Ft (m) Min. Length Total Ft (m)

Max. Pipe Height Difference Between Outdoor Unit & Farthest Indoor Ft (m) Max. Pipe Height Difference Between Indoor Units Ft (m) Connection Method

Conn. Pipe Diameter Inch

Min. Length Each Ft (m)

Net Weight Ibs. (kg) Dimensions: Height Inch mm Width Inch Depth Inch mm

Refrigerant

18RLXFZH	24RLXFZH					
Heat Pump	Heat Pump					
2	2 to 3					
14,000 to 21,000	14,000 to 27,000					
18,000/22,000	22,000/25,000					
14 to 115	14 to 115					
(-10 to 46)	(-10 to 46)					
-15 to 75	-15 to 75					
(-26 to 24)	(-26 to 24)					
1.33/1.70	1.65/1.81					
208-230/60/1	208-230/60/1					
16.4	20.8					
19.7	25.1					
20	30					
1,648/1,648	1,942/1,942					
Propeller x 1	Propeller x 1					
48	50 52					
50						
98 (30)	98 (30)					
164 (50)	230 (70)					
82 (25)	82 (25)					
49 (15)	49 (15)					
16 (5)	16 (5)					
49 (15)	49 (15)					
33 (10)	33 (10)					
Flare	Flare					
Lig. 1/4 x 2	Liq. 1/4 x 3					
Suc. 3/8 x 2	Suc. 1/2 x 1,					
	3/8 x 2					
134 (61)	146 (66)					
32-11/16	32-11/16					
830	830					
35-7/16	35-7/16					
900	900					
13	13					
330	330					
R410A	R410A					

Nominal Capacities, SEER and HSPF Ratings

Data below is based on AHRI 210/240 non-ducted wall mounted models.

Model	Indoor Unit		Cooling Capacity Btu/h	EER	SEER	Heating Rated Capacity Btu/h		Heating Maximum Capacity Btu/h		СОР	HSPF
	Type	Combination	95°F			47°F	17°F	17°F	5°F	47°F	
AOU18RLXFZH	Non-Ducted	9+9	18,000	13.5	21.5	22,000	14,200	23,600	22,000	3.79	10.3
	Ducted	9+9	18,000	12.4	19.0	22,000	14,200	23,600	22,000	3.60	9.0
	Mixed	9+9	18,000	13.0	20.3	22,000	14,200	23,600	22,000	3.70	9.7
AOU24RLXFZH	Non-Ducted	9+7+7	22,000	13.3	20.0	25,000	15,400	26,400	25,000	4.04	10.3
	Ducted	9+7+7	22,000	12.1	18.0	25,000	15,400	26,400	25,000	3.87	9.0
	Mixed	9+7+7	22,000	12.7	19.0	25,000	15,400	26,400	25,000	3.96	9.7

Yellow rows represent models that are ENERGY STAR® qualified.