



# SUBMITTAL INFORMATION

## Angle Ball Service Valves - (BA41-xxxW-G-NL style)



### GRIP JOINT FOR COPPER OR PLASTIC TUBING (CTS) INLET BY FEMALE IRON PIPE THREAD OUTLET



| VALVE SIZE | INLET SIZE | OUTLET SIZE | LENGTH   | HEIGHT   | APPROX. WT. LBS | PART NUMBER    | ✓ SUBMITTED ITEM(S) |
|------------|------------|-------------|----------|----------|-----------------|----------------|---------------------|
| 3/4"       | 3/4"       | 3/4"        | 1-17/32" | 1-7/8"   | 2.0             | BA41-333W-G-NL |                     |
| 1"         | 1"         | 1"          | 1-23/32" | 2-29/64" | 2.5             | BA41-444W-G-NL |                     |

**Note:** Ford recommends using insert stiffeners with plastic pipe or tubing.

### FEATURES

- All brass that comes in contact with potable water conforms to AWWA Standard C800 (UNS No. C89833)
- The product has the letters "NL" cast into the main body for lead-free identification
- Certified to NSF/ANSI Standard 61 and NSF/ANSI Standard 372 where applicable
- Brass components that do not come in contact with potable water conform to AWWA Standard C800 (ASTM B62 and ASTM B584, UNS No. C83600, 85-5-5-5)
- Ends are integral or secured with adhesive to prevent unintentional disassembly
- Hole for attaching handle is provided in tee-head
- 300 PSI working pressure
- Padlock Wing for locking valve in closed position

**Note:** Recommended flow from inlet to outlet

**Optional full 360° tee-head rotation.** Insert "R" into part number. Example: BA41-444WR-Q-NL

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



**The Ford Meter Box Company, Inc.**  
P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443  
Phone: 260-563-3171 / Fax: 800-826-3487  
Overseas Fax: 260-563-0167  
www.fordmeterbox.com

03/22/17

Submitted By: