



Tripoint[™]DC 1/8 GPF Urinal Flushometer K-10949-SV

Features

- Fixture-mount design.
- Includes 1.5V AA batteries.

Material

Brass construction.

Technology

- Electronic infrared sensor with TriPoint[™] technology for accurate activation.
- Slow-closing piston technology.

Installation

 Intended for urinal installations with 3/4" spud coupling connection

Optional Accessories

GP1118986 Flushometer Extension Kit





ADA CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1 CSA B64 ASSE 1037 EPA WaterSense® ADA ICC/ANSI A117.1 CSA B651 OBC

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color Code Description


CP

Polished Chrome





Tripoint™DC 1/8 GPF Urinal Flushometer K-10949-SV



Technical Information

All product dimensions are nominal.

Pressure and Supply Requirements

Fixture flow rate min: 10 gpm (37.9 lpm) Fixture pressure max 80 psi (551.6 kPa)

(static):

Power source: AA 1.5 V, included

Notes

Install this product according to the installation guide.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

