

K. O.DIRT BLASTER™

Dirt and Grease Stripper

<u>Description</u> | <u>Characteristics</u> | <u>Applications</u> | <u>Packaging</u> | <u>Instructions</u> | <u>Precautions</u> | <u>Specifications</u> | <u>Limited Warranty</u>

DESCRIPTION:

K.O. DIRT BLASTER™ is a high pressure cleaner and degreaser for small condenser coils found in restaurant and food service refrigeration, air conditioning, electrical and mechanical equipment. K.O. Dirt Blaster™ strips off dirt and cooking grease without a water rinse. It contains a quick drying safety solvent and has a pleasant citrus scent. Its high dielectric strength and non-flammable formula is great for most coil cleaning applications.

Top of Page

CHARACTERISTICS:

- · Dissolves grease quickly
- Pressure washes small condenser coils without a water rinse
- Quick Drying
- Pleasant citrus scent
- Non-Flammable
- Safety Degreaser Solvent
- No CFC's

Top of Page

APPLICATIONS:

K.O. Dirt Blaster™ quickly dissolves grease and oil on refrigeration coils, oil burner surfaces and other machine parts. K.O. Dirt Blaster™ is non conductive, so it will not short out electrical equipment such as switches, relays, circuit breakers, motors and electrical components. It is particularly effective on restaurant grease and other greasy surfaces.

Top of Page

PACKAGING:

Code	Size	Qty. Per Case	Lbs. per Case	Cu. Ft Per Case
88438	20 oz. (568 g)	12	19	0.52

Top of Page

INSTRUCTIONS:

Read all label warnings and directions before using. Do not use on hot surfaces or on plastic or paint before testing.

Removes wax finishes.

FOR USE ON CONDENSER COILS

- 1. Shut off equipment.
- 2. Loosened debris may be pushed through coil fins or may cause dripping or staining. Place cardboard behind coil

to block any loosened debris or used products.

- 3. Saturate condenser coil with K.O.™ Dirt Blaster.
- 4. Wait at least 5 minutes before starting up equipment.
- 5. Although K.O. Dirt Blaster™ needs no rinsing or wiping, water pressure may be used to float out debris.

FOR USE ON OIL BURNER AND ALL OTHER EQUIPMENT

1. Spray on. The heavier the dirt and grease layer, the heavier the spray.

2. For heavy films and tars, allow 5 minutes soaking time, then wipe or flush off.

For best results use only on cool surfaces.

For additional technical information, call Toll Free 1-800-231-3345.

Top of Page

PRECAUTIONS:

FOR CHEMICAL EMERGENCY, SPILL, LEAK, FIRE, EXPOSURE OR ACCIDENT,

CALL CHEMTREC - DAY OR NIGHT 1-800-424-9300

VAPOR HARMFUL

CONTAINS: Methylene chloride. PRECAUTIONS: Do not puncture or burn container. Harmful if swallowed or inhaled. May cause eye and skin irritation. Aerosol may form explosive mixture with air when used. Use only with good ventilation. Wear adequate protective gear and clothing. Avoid contact with eyes and skin. Wash after handling. FIRST AID: For any overexposure, get immediate medical attention after first aid is given. Eyes - Flush 15 minutes with clean water. Skin - Wash with soap and water. Inhalation - Remove to fresh air. Ingestion - Only if conscious, give large amounts of water. If unconscious, do not give anything by mouth or attempt to induce vomiting. Seek immediate medical attention. FIRE AND SPILLS: For fire, use water fog, CO2, foam, or dry chemicals. STORAGE AND HANDLING: Store in a cool, well ventilated area. Keep container upright and tightly closed. Do not expose to heat or store at temperatures above 120 degree F. KEEP OUT OF REACH OF CHILDREN.

For additional information, refer to Material Safety Data Sheet.

Top of Page

SPECIFICATIONS:

Flash Point SETA CC None

Color Colorless
Shelf Life 2 years

Suggestions and recommendations covering the use of our products are based on our past experience and laboratory findings. However, as we have no control as to the methods and conditions of application, we only assume responsibility for the uniformity of our products within manufacturing tolerances.

Top of Page

LIMITED WARRANTY:

RectorSeal® makes the Limited Express Warranty that when the instructions for storage and handling of our products are followed we warrant our products to be free from defects. THIS LIMITED EXPRESS WARRANTY IS EXPRESSLY IN LIEU OF ANY OTHER EXPRESS OR IMPLIED WARRANTIES, INCLUDING ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, AND OF ANY OTHER OBLIGATION ON THE PART OF RECTORSEAL®. The sole remedy for breach of the Limited Express Warranty shall be the refund of the purchase price. All other liability is negated and disclaimed, and RectorSeal® shall not be liable for incidental or consequential damages.

Top of Page

MANUFACTURED IN U.S.A. BY

RectorSeal_®

2601 Spenwick Drive • Houston, TX 77055 USA 713-263-8001 • Fax 713-263-7577 Toll-free 800-231-3345 • Fax 800-441-0051

<u>Back</u>