



Product Specifications for E22392-10PC

Job Name:	Job Type:
Quantity:	Comments:



E22392-10PC
Wand LED Bath Vanity

Finish
Polished Chrome

Glass/Shade
Clear/White

Product Category
Bath Vanity

Lamping

Number of Bulb(s)	1
Light Type	LED
Bulb Type	LED
Max Bulb Wattage	10
Max Fixture Wattage	10
Rated Life	±40,000 Hours
Rated Lumens	±880
Color Temp	±3,000 K
Bulb(s) Included	Yes
Light Up/Down	N/A
Beam Spread	N/A
CRI	N/A
Photo Cell Included	N/A
Ballast/Driver/Transformer	Yes
Dimmable	Lutron® CL or Leviton® LED Dimmer

Measurements

Width	24.00"
Height	4.75"
Length	N/A
Extension	2.50"
Back Plate Width	N/A
Back Plate Height	N/A
HCO	2.37"
Min Overall Height	N/A
Max Overall Height	N/A
Hanging Weight	2.86 lb(s)
Height Adjustable	N/A
Slope	N/A
Chain Length	N/A
Wire Length	N/A
Canopy Width	
Canopy Height	
Canopy Length	N/A

Shipping

Carton Weight	3.63 lb(s)
Carton Width	6.50"
Carton Height	4.92"
Carton Length	27.17"
Carton Cubic Feet	N/A
Master Pack	1
Master Pack Weight	N/A
Master Pack Width	N/A
Master Pack Height	N/A
Master Pack Length	N/A
Master Cubic Feet	N/A
UPS Shippable	Yes

Certification

Safety Rating	Damp
Energy Star	No
CA Title 24	No
CA Title 20	No
ADA	Yes

Other

UPC Code	845094054511
Material	N/A

Equivalents

Incandescent Watts	N/A
Fluorescent Watts	N/A

ET2 Contemporary Lighting and all designs, logos and images © 2015 ET2 Contemporary Lighting. All Rights Reserved. ET2 Contemporary Lighting reserves the right, at any time, to make changes in the design and/or construction of the product including the discontinuation of product without prior notice. Color may vary from what is pictured above due to limitations inherent to photographic processes. Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do the installation. Always install to a mechanically sound structure.