For Residential and Commercial Applications

Job Name	Engineer / Architect	
Job Location	Wholesaler	
Submittal Date	Contractor	

68 Series Compression x Male Iron Pipe Adapters


Use: For use with instrumentation, hydraulic and pneumatic systems. Designed for use with aluminum, copper and plastic tubing. Not intended for use with steel tubing

* Plastic tubing requires a plastic insert and a sleeve (see 60PT & 63PT submittal forms for details)

Design Features:

- **Little to no tube preparation.** Compression fittings do not require flaring, soldering or other types of tube preparation
- Available in a broad range of sizes
- Compliant fitting options available for California and Vermont "low-lead" requirements





Operating Specifications:

Temperature: -65°- 250°F at maximum operating pressures

Working Pressure: See chart below

Vibration: Fair vibration resistance

WORKING PRESSURE			
PSI	Tube O.D.	Tube Wall (Inches)	
400	1/8	0.030	
400	3/16	0.030	
300	1/4	0.030	
300	5/16	0.032	
200	3/8	0.032	
200	1/2	0.032	
150	5/8	0.035	
100	3/4	0.035	
75	7/8	0.035	



Standard Fitting

MATERIAL SPECIFICATIONS			
Fitting Body	C36000 brass		
Compression Sleeve	C36000 brass		
Compression Nut	C36000 brass		
Option	Chrome plating		

Compliant Fitting

MATERIAL SPECIFICATIONS			
Fitting Body	Compliant brass		
Compression Sleeve	C36000 brass		
Compression Nut	C36000 brass		
Option	Chrome plating		

Standard Part Listing:

Ш	68-2-2	1/8" OD Tube x 1/8" M.I.P.
	68-2-2 B	1/8" OD Tube x 1/8" M.I.P., bulk
	68-2-2-1 B	1/8" OD Tube x 1/8" M.I.P body only, bulk

This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.




68 Series Compression x Male Iron Pipe Adapters

Standard Part Listing (con't):

	31 7
68-4-4	1/4" OD Tube x 1/4" M.I.P.
68-4-4 B	1/4" OD Tube x 1/4" M.I.P., bulk
68-4-4-1 B	1/4" OD Tube x 1/4" M.I.P body only, bulk
68-6-6	3/8" OD Tube x 3/8" M.I.P.
68-6-6 B	3/8" OD Tube x 3/8" M.I.P., bulk
68-6-6-1 B	3/8" OD Tube x 3/8" M.I.P body only, bulk
68-6-6-1 CB	3/8" OD Tube x 3/8" M.I.P body only, chrome plated, bulk
68-8-8	1/2" OD Tube x 1/2" M.I.P.
68-8-8 B	1/2" OD Tube x 1/2" M.I.P., bulk
68-8-8 C	1/2" OD Tube x 1/2" M.I.P., chrome plated
68-8-8-1 B	1/2" OD Tube x 1/2" M.I.P body only, bulk
68-12-12	3/4" OD Tube x 3/4" M.I.P.
68-12-12-1 B	3/4" OD Tube x 3/4" M.I.P body only, bulk

Compliant Part Listing:

•	9
68-4-4X	1/4" OD Tube x 1/4" M.I.P.
68-6-6X	3/8" OD Tube x 3/8" M.I.P.
68-6-6X C	3/8" OD Tube x 3/8" M.I.P., chrome plated
68-6-6X CB	3/8" OD Tube x 3/8" M.I.P., chrome plated, bulk
68-8-8X	1/2" OD Tube x 1/2" M.I.P.
68-8-8-1X B	1/2" OD Tube x 1/2" M.I.P body only, bulk



Listings & Certifications:

 Compliant product CSA approved to California Health & Safety Code and Vermont Bill S.152 (Project # 2174785)

PART DIMENSIONS (Inches)			
Model	DIM. A	DIA. B	DIM. C
68-2-2	0.79	0.94	7/16
68-4-4	0.88	0.187	9/16
68-6-6	1.06	0.312	11/16
68-8-8	1.22	0.437	7/8
68-12-12	1.38	0.562	1-1/16

This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

