

B7 STUD BOLT PRE-PACKAGED FLANGE KITS

Features

- Material Test Reports (MTRs) in the Box
- Pre-package kits for ANSI class 150# and 300# Flanges
- · Bagged & Packed in Double-Walled Strapped Cartons
- · Studs:
 - o Grade B7
 - Full Threaded Rod Stud Bolts
 - o Chamfered Flat Faced Ends
 - Manufactured from Chromium-Molybdenum Ferritic Alloy Steel
 - o Tensile Strength: 125 KSI Min.
 - o Hardness 35 HRC Max.
- · Nuts:
 - o Grade 2H
 - o Heavy Hex
 - o Single-Chamfered with Bottom Washer Face
 - Manufactured from Carbon Steel
 - o Rockwell Hardness: C24 to C38
- · Threads:
 - 1" Diameter & Smaller Unified Inch Coarse Series (UNC), Class 2A
 - 1-1/8" Diameter Unified Inch 8 Thread Series (UN8), Class 2A
- · Plain Finish Coated with Light Protective Oil
- Right Hand Threads
- · Heat Treated
- Manufacturer Identification and Grade Marks on All Studs and Nuts
- · Studs and Nuts are Heat Code Traceable*
- Stud and Nut Sets are Lot Number Traceable*

Standards

1 FLANGE KIT

- · Studs:
 - o Material & Mechanical Properties: ASTM A193 Grade B7
 - o Threads: ASME B1.1, UNC or UN8, Class 2A
- Nuts:
 - o Material & Mechanical Properties: ASTM A194 Grade 2H
 - o Dimensions: ASME B18.2.2
- * Heat codes and lot numbers are listed on box labels. MTRs are included in each kit.



NOTE: Figure B7K flange kits are

tagged with a yellow label to indicate



Markings

Studs and nuts are marked per ASTM requirements

- Manufacturer Mark: HY (hex nut marks can vary)
- Stud Grade Mark: B7
- · Hex Nut Grade Mark: 2H



Figure Number Matrix

FNW	B7K <u>1</u> <u>X</u>	
FLANGE CLASS	FLANGE	SIZE
1 = 150#	1/2" = D	3" = M
3 = 300#	3/4" = F	4" = P
	1" = G	5" = S
	1-1/4" = H	6" = U
	1-1/2" = J	8" = X
	2" = K	10" = 10
	2-1/2" = L	12" = 12


B7 STUD BOLT PRE-PACKAGED FLANGE KITS

Part Numbers & Dimensions

	150#						
Flange Size	Part Number	D (inch) (UNC)	L (inch)	F (inch)	H (inch)	Qty/ Kit	Wt. (lbs)
1/2	FNWB7K1D	1/2 - 13	2 1/2	7/8	31/64	4	1.07
3/4	FNWB7K1F	1/2 - 13	2 1/2	7/8	31/64	4	1.07
1	FNWB7K1G	1/2 - 13	2 1/2	7/8	31/64	4	1.07
1-1/4	FNWB7K1H	1/2 - 13	2 3/4	7/8	31/64	4	1.12
1-1/2	FNWB7K1J	1/2 - 13	3	7/8	31/64	4	1.16
2	FNWB7K1K	5/8 - 11	3 1/4	1-1/16	39/64	4	2.04
2-1/2	FNWB7K1L	5/8 - 11	3 1/2	1-1/16	39/64	4	2.11
3	FNWB7K1M	5/8 - 11	3 1/2	1-1/16	39/64	4	2.11
4	FNWB7K1P	5/8 - 11	3 3/4	1-1/16	39/64	8	4.37
5	FNWB7K1S	3/4 - 10	3 3/4	1-1/4	47/64	8	6.72
6	FNWB7K1U	3/4 - 10	4	1-1/4	47/64	8	6.93
8	FNWB7K1X	3/4 - 10	4 1/4	1-1/4	47/64	8	7.15
10	FNWB7K110	7/8 - 9	4 1/2	1-7/16	55/64	12	15.98
12	FNWB7K112	7/8 - 9	4 3/4	1-7/16	55/64	12	16.43

	300#						
Flange Size	Part Number	D (inch) (UNC)*	L (inch)	F (inch)	H (inch)	Qty/ Kit	Wt. (lbs)
1/2	FNWB7K3D	1/2 - 13	2 1/2	7/8	31/64	4	1.07
3/4	FNWB7K3F	5/8 - 11	3	1-1/16	39/64	4	1.96
1	FNWB7K3G	5/8 - 11	3	1-1/16	39/64	4	1.96
1-1/4	FNWB7K3H	5/8 - 11	3 1/4	1-1/16	39/64	4	2.04
1-1/2	FNWB7K3J	3/4 - 10	3 1/2	1-1/4	47/64	4	3.25
2	FNWB7K3K	5/8 - 11	3 1/2	1-1/16	39/64	8	4.22
2-1/2	FNWB7K3L	3/4 - 10	4	1-1/4	47/64	8	6.93
3	FNWB7K3M	3/4 - 10	4 1/4	1-1/4	47/64	8	7.15
4	FNWB7K3P	3/4 - 10	4 1/2	1-1/4	47/64	8	7.37
5	FNWB7K3S	3/4 - 10	4 3/4	1-1/4	47/64	8	7.52
6	FNWB7K3U	3/4 - 10	4 3/4	1-1/4	47/64	12	11.28
8	FNWB7K3X	7/8 - 9	5 1/2	1-7/16	55/64	12	17.77
10	FNWB7K310	1 - 8	6 1/2	1-5/8	63/64	16	35.33
12	FNWB7K312	1-1/8 - 8	6 3/4	1-13/16	1-7/64	16	48.12

^{*} Diameters 1-1/8" and larger are UN8



Notes:

- 1. Diameters (D) up to and including 1" are UNC, Class 2A, per ASME B1.1.
- 2. Diameters (D) 1-1/8" are UN8, Class 2A, per ASME B1.1.
- 3. Lengths (L) are effective thread lengths, excluding end points. Overall stud bolt length will be longer.
- 4. Heavy hex nut dimensions are nominal per ASME B18.2.2.

© 2013 - FNW. All rights reserved.

The FNW logo is a trademark of Ferguson Enterprises, Inc., PL Sourcing, PO Box 2778, Newport News, VA 23609

The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, expressed or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice. Always verify that you have the most recent product specifications or other documentation prior to the installation of these products.

DOC: FNWB7K13 Ver. 4/2013