


PRODUCT SUBMITTAL 300

Product: EVERLOC[®] Sleeve

Date: 14-October-09 (supersedes, 20-September-07)



Article No.	Sleeve Size	A in. (mm)	B in. (mm)	C in. (mm)
243507	3/8"	0.787 (20.0)	0.750 (19.0)	0.529 (13.4)
260077	1/2"	0.787 (20.0)	0.846 (21.5)	0.650 (16.5)
243607	5/8"	0.906 (23.0)	1.100 (28.0)	0.778 (19.7)
260577*	3/4"	0.906 (23.0)	1.102 (28.0)	0.902 (23.0)
260877*	1"	1.240 (31.5)	1.378 (35.0)	1.154 (29.3)
235507	1 1/4"	1.425 (36.2)	1.690 (43.0)	1.426 (36.2)
235707	1 1/2"	1.493 (38.0)	1.929 (49.0)	1.694 (43.0)
235907	2"	1.740 (44.2)	2.488 (63.2)	2.205 (56.0)

TECHNICAL DESCRIPTION

Specification	ASTM F 2080 / F 877	
Material	aterial Machined From Brass Rod	
Certifications	ASTM F 877 / F 2080 / CSA B 137.5 /	
	ICC ESR-1576 / *UL 1821 / *ULC/ORD C199P	

FUNCTIONAL DESCRIPTION

EVERLOC compression-sleeve fittings are ideal for fire protection (sizes indicated with *), heating, snow and ice melting and hydronic radiator connections, when used with RAUPEX[®] PEXa pipes. EVERLOC fittings and compression-sleeves ("sleeves") create reliable connections that can be embedded directly in a thermal mass (when wrapped in chloride-free tape or RAUCROSS[™] heat shrink tubing for corrosion protection – check local codes for compliance), or walled in. EVERLOC sleeves are machined from brass rod.

Installation is performed with REHAU's EVERLOC tools. Follow all published installation instructions.

The information contained herein is believed to be reliable, but no representations, guarantees or warranties of any kind are made as to its accuracy, suitability for particular applications or the results to be obtained therefrom. Before using, the user will determine suitability of the information for user's intended use and shall assume all risk and liability in connection therewith. To the extent permitted by law, REHAU INCOMPACIAIMS ALL IMPLIED WARRANTIES, INCLUDING BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR OF FITNESS FOR A PARTICULAR PURPOSE.

For updates to this publication, visit na.rehau.com/resourcecenter