Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

## **LEAD FREE**\*

## **Series LF909**

## Reduced Pressure Zone Assemblies

Sizes: 21/2" - 10"

Series LF909 Reduced Pressure Zone Assemblies are designed to provide cross-connection control protection of the potable water supply in accordance with national plumbing codes. This series can be utilized in a variety of installations, including health hazard cross-connections in plumbing systems or for containment at the service line entrance. With its exclusive relief valve design incorporating the "air-in/water-out" principle, it provides substantially improved relief valve discharge performance during the emergency conditions of combined backsiphonage and backpressure with both checks fouled. The LF909 features Lead Free\* construction to comply with Lead Free\* installation requirements.

Series LF909 is also available with SentryPlus™ Alert technology to detect catastrophic relief valve discharge that could potentially cause flooding, and issue a multi-channel alert (call, e-mail, text) to selected users so they can take action to avoid potentially costly flooding.


#### **Features**

- Replaceable seats
- Stainless steel internal parts
- No special tools required for servicing
- Captured spring check assemblies
- Fused epoxy coated & lined checks
- Industrial strength sensing hose
- Field reversible relief valve
- Air-in/water-out relief valve design provides maximum capacity during emergency conditions

### **Specifications**

A Reduced Pressure Zone Assembly shall be installed at each cross-connection to prevent backsiphonage and backpressure backflow of hazardous materials into the potable water supply. The assembly shall consist of a pressure differential relief valve located in a zone between two positive seating check valves and captured springs. Backsiphonage protection shall include provision to admit air directly into the reduced pressure zone via a separate channel from the water discharge channel. The assembly shall include two tightly closing shutoff valves before and after the valve and test cocks. The Lead Free\* Reduced Pressure Zone Assembly shall comply with state codes and standards, where applicable, requiring reduced lead content. The assembly shall meet the requirements of ASSE Std. 1013; AWWA Std. C511-92; CSA B64.5; and UL Classified File No. EX3185. Listed by IAPMO (UPC). Approved by the Foundation for Cross-Connection Control and Hydraulic Research at the University of Southern California. The assembly shall be a Watts Series LF909.





# Now Available WattsBox Insulated Enclosures.

For more information, send for literature ES-WB.

#### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

#### NOTICE

Inquire with governing authorities for local installation requirements

\*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.



#### **Available Models & Options**

Suffix:

LF – without shutoff valves

NRS – non-rising stem resilient seated gate valves
OSY - UL/FM outside stem & yoke resilient seated gate

valves

QT-FDA – FDA epoxy coated quarter-turn ball valves

S-FDA – FDA epoxy coated strainer

ALERT with SentryPlus™ Alert flood detection system

Note: The installation of a drain line is recommended. When installing a drain line, an air gap is necessary.

#### **Materials**

Check Valve Bodies: FDA epoxy coated cast iron

Seats: Stainless steel Trim: Stainless steel

Relief Valve Body: 21/2"-3" Lead Free\* cast copper silicon alloy

4"-10" FDA epoxy coated cast iron

Test Cocks: Lead Free\* copper silicon alloy

#### Pressure — Temperature

Temperature Range: 33°F-110°F (0.5°C-43°C) continuous,

140°F (60°C) intermittent

Maximum Working Pressure: 175psi (12.06 bar)

#### **Standards**

AWWA C511-92

IAPMO PS 31, SBCCI (Standard Plumbing Code)
USC manual for Cross-Connection Control, 8th Edition

### **Approvals**












Approved by the Foundation for Cross-Connection Control and Hydraulic Research at the University of Southern California.


## **How It Operates**


The unique relief valve construction incorporates two channels: one for air, one for water. When the relief valve opens, as in the accompanying air-in/water-out diagram, the right-hand channel admits air to the top of the reduced pressure zone, relieving the zone vacuum. The channel on the left then drains the zone to atmosphere. Therefore, if both check valves foul, and simultaneous negative supply and positive backpressure develops, the relief valve uses the air-in/water-out principle to stop potential backflow.



Water Air Out In

## Dimensions - Weights





Watts G-4000 Series Ball Valves Send for F-G4000



NOTE: Valve may be furnished with (2) OSY or (2) NRS Shutoffs.

NOTE: Relief valve section is reversible, therefore, can be on either side and is furnished standardly as shown. Carla.Long@wattswater.com

SIZE	DIMENSIONS											WEIGHT														
					C clearance																					
					for check																					
	Α	١	A	A1 (OSY)* (NRS)		S)	D L		U		R		R (QT)		T		NRS		OSY		QT					
in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs.	lbs.	kgs.	lbs.	kgs.
21/2	411/2	1053	203/4	527	16%	416	9%	238	51/4	133	<b>26</b> 5/16	669	11	279	4	102	16	406	91/16	230	195	88.4	198	89.8	182	82.6
3	421/2	1079	211/4	539	187//8	479	101/4	260	51/4	133	<b>26</b> 5/16	669	11	279	5	127	16	406	91/16	230	225	102	230	104	190	86
4	555/16	1405	<b>27</b> <sup>2</sup> / <sub>3</sub>	702	223/4	578	<b>12</b> <sup>3</sup> / <sub>16</sub>	310	6	152	373/16	944	14	356	6	152	19¾	502	14%	365	455	206	470	213	352	160
6	65 <sup>13</sup> / <sub>16</sub>	1672	33	836	301//8	765	16	406	6	152	4411/16	1134	16	406	11	279	26	660	14%	365	718	326	798	362	762	346
8	78%16	1995	395/16	998	37¾	959	19 <sup>15</sup> / <sub>16</sub>	506	93/4	248	555/16	1404	21	533	111/4	286	1111/4	286	191/4	489	1350	612	1456	660	2286	1037
10	93%16	2376	46¾	1188	45¾	1162	2313/16	605	93/4	248	675/16	1709	21	533	121/2	318	121/2	318	21	533	2160	980	2230	1011	3716	1685

<sup>\*</sup>UL, FM approved backflow preventers must include UL/FM approved OSY gate valves.

#### **Strainer Dimensions**

SIZE		WEIGHT						
	l l	Л	N.	1†	1	V		
in.	in.	mm	in.	mm	in.	mm	lbs.	kgs.
21/2	10	254	10	254	61/2	165	28	12.7
3	101//8	257	10	254	7	178	34	15.4
4	121/8	308	12	305	81/4	210	60	27
6	181/2	470	20	508	13½	343	133	60
8	21%	549	223/4	578	15½	394	247	112
10	26	660	28	711	181/2	470	370	168

<sup>† –</sup> Dimension required for screen removal

## Air Gap Dimensions

When installing a drain line on Series 909 backflow preventers that are installed horizontally, use 909 AG series air gaps.


IRON BODY Model No.	ORDERING CODE	SERIES/SIZES			WEIGHT					
				А	1	В		С		
			in.	mm	in.	mm	in.	mm	lbs	kgs
909AG-F	881378	11/4" - 3" 009/909	43//8	111	63/4	171	2	51	3.25	1.47
		11/4" – 2" 009 M1								
		2" 009 M2								
909AG-K	881385	4" - 6" 909	63/8	162	9%	244	3	76	6.25	2.83
		8" - 10" 909 M1								
909AG-M	881387	8" – 10" 909	7%	187	1111/4	286	4	102	15.5	7.03

For flange size backflow preventers installed vertically (flow down), a fabricated air gap is recommended.



## Capacity

\*Typical maximum flow rate (7.5 feet/sec.)





USA: Tel: (978) 689-6066 • Fax: (978) 975-8350 • Watts.com
Canada: Tel: (888) 208-8927 • Fax: (888) 479-2887 • Watts.ca
Latin America: Tel: (52) 55-4122-0138 • Watts.com

ES-LF909L 2008 © 2020 Watts