



Gem • 2 110 S.S. — Rev. 1 (06/01) Copyright © 2001 SLOAN VALVE COMPANY Printed in the U.S.A.

Gem·2® Model Flushometer



Description

Exposed, Water Closet Flushometer, for floor mounted or wall hung top spud bowls.

Flush Cycle

- ☐ Model 110 Water Saver (3.5 gpf/13.2 Lpf)
- ☐ Model 111 Low Consumption (1.6 gpf/6.0 Lpf)

Specifications

Quiet, Exposed, Piston Type, Chrome Plated Closet Flushometer with the following features:

- Fixed Volume Piston with Filtered O-Ring By-Pass
- ADA Compliant Metal Oscillating Handle
- 1" I.P.S. Screwdriver Bak-Chek™ Angle Stop
- Vandal Resistant Stop Cap
- · Adjustable Tailpiece
- Vacuum Breaker Flush Connection
- $\bullet\,$ Spud Coupling, Wall and Spud Flange for 1½" Top Spud
- High Copper, Low Zinc Brass Castings for Dezincification Resistance
- Non-Hold-Open Handle and No External Volume Adjustment to Ensure Water Conservation
- Handle Packing, Stop Seat and Vacuum Breaker to be Molded from PERMEX™ Rubber Compound for Chloramine Resistance

Valve Body, Cover, Tailpiece and Control Stop shall be in conformance with ASTM Alloy Classification for Semi-Red Brass. Valve shall be in compliance to the applicable sections of ASSE 1037, ANSI/ASME 112.19.6, and Military Specification V-29193.

Variations

\Box U	11/4" Flush Connection and Spud Coupling
□ TP	Trap Primer
□ XYV	Less Vacuum Breaker
□ YB	Sweat Solder Adapter Kit
☐ YBYC	Sweat Solder Adapter & Cast Set Screw Wall Flange
□ YG	Extended Bumper on Angle Stop (for seat with cover)
□YJ	Split Ring Pipe Support
□ YK	Solid Ring Pipe Support
□ YO	Bumper on Angle Stop

NOTE: Bak-Chek™ Angle Stop available with 1" Whitworth Thread (please specify).

See Accessories Section of the Sloan catalog for details on these and other Flushometer variations.



This space for Architect/Engineer approval

The information contained in this document is subject to change without notice.



Made in the U.S.A.

SLOAN VALVE COMPANY • 10500 SEYMOUR AVE. • FRANKLIN PARK, IL. 60131 Ph: 1-800-9-VALVE-9 or 1-847-671-4300 • Fax: 1-800-447-8329 or 1-847-671-4380 http://www.sloanvalve.com