



Product Specifications for E22779-91PC

Job Name:	Job Type:
Quantity:	Comments



E22779-91PC Fizz IV 9-Light LED Pendant

Finish
Polished Chrome

Glass/Shade
Bubble

Product Category
Multi-Light Pendant

Lamping

Number of Bulb(s)	9
Light Type	LED
Bulb Type	LED
Max Bulb Wattage	7.5
Max Fixture Wattage	67.50
Rated Life	±40,000 Hours
Rated Lumens	±2,142
Color Temp	±3,000 K
Bulb(s) Included	Yes
Light Up/Down	N/A
Beam Spread	N/A
CRI	N/A
Photo Cell Included	N/A
Ballast/Driver/Transformer	Yes
Dimmable	Standard/Lutron® CL or Leviton® LED

Measurements

Width	16.00"
Height	14.00"
Length	N/A
Extension	N/A
Back Plate Width	N/A
Back Plate Height	N/A
HCO	N/A
Min Overall Height	N/A
Max Overall Height	134.00"
Hanging Weight	27.69 lb(s)
Height Adjustable	N/A
Slope	N/A
Chain Length	N/A
Wire Length	120.00"
Canopy Width	N/A
Canopy Height	N/A
Canopy Length	N/A

Shipping

Carton Weight	30.80 lb(s)
Carton Width	21.50"
Carton Height	7.50"
Carton Length	23.50"
Carton Cubic Feet	N/A
Master Pack	1
Master Pack Weight	N/A
Master Pack Width	N/A
Master Pack Height	N/A
Master Pack Length	N/A
Master Cubic Feet	N/A
UPS Shippable	Yes

Certification

Safety Rating	Dry
Energy Star	No
CA Title 24	No
CA Title 20	No
ADA	No

Other

UPC Code	845094060369
Material	N/A

Equivalents

Incandescent Watts	201.27
Fluorescent Watts	44.28

ET2 Contemporary Lighting and all designs, logos and images © 2015 ET2 Contemporary Lighting. All Rights Reserved. ET2 Contemporary Lighting reserves the right, at any time, to make changes in the design and/or construction of the product including the discontinuation of product without prior notice. Color may vary from what is pictured above due to limitations inherent to photographic processes. Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do the installation. Always install to a mechanically sound structure.