
American Standard

Style That Works Better

### QUENTIN<sup>™</sup> TWO-HANDLE THERMOSTAT WITH SEPARATE VOLUME CONTROL



#### **GENERAL DESCRIPTION:**

Cast brass valve body. The single unit contains two handles, the bottom lever handle sets the desired temperature and the top lever handle functions as an on/off, volume control. The temperature is maintained by a wax element moving a shuttle valve between hot and cold. The volume is controlled by twin ceramic disc valve cartridges. Ceratherm includes Hot Limit Safety Stop. Maximum temperature limit is 112°F. Escutcheon plate is stamped brass. Available with 1/2" or 3/4" NPT inlets and outlets. The valve has a high flow rate, ideal for mutiple outlet installations.

#### **PRODUCT FEATURES:**

**Brass Casting:** Highest quality faucet material for durability & long life.

**Wax Thermostatic Unit:** Permits shuttle valve to move between the hot and cold seat to maintain the pre-selected constant water temperature.

Back to Back Capable: Hot and cold can be reversed.

**Spring-Loaded Check Valves:** When the hot and cold water enters the fitting, both supplies pass through the spring-loaded check valves to prevent cross flow of hot and cold water.

Integrated Stop Valves: Ensure easy cleaning and servicing.

Adjustable Hot Limit Safety Stop: Limits the amount of hot water allowed to mix with cold. Reduces the risk of accidental scalding. Maximum water temperature limit may be reduced to 104 or 109 degrees Fahrenheit.

#### SUGGESTED SPECIFICATION:

Two handle Thermostat shall feature a cast brass valve body. Thermostat shall be a wax element shuttle valve. Shall also feature ceramic disc valving, 1/2" NPT or 3/4" NPT inlets and outlets. Fitting shall be American Standard Model # T440.740.\_\_\_\_ (Trim Kit) and R520 or R540 (Rough Valve).




Style That Works Better

## QUENTIN<sup>™</sup> TWO-HANDLE THERMOSTAT WITH SEPARATE VOLUME CONTROL

# **CODES AND STANDARDS**

These products meet or exceed the following codes and standards:

ASSE 1016 ASME A112.18.1 CSA B125.1



14				Finish Options		
<its**< th=""><th>Product</th><th></th><th>Polished Chrome</th><th>Oil Rubbed Bronze</th><th>PVD Satin Nickel</th></its**<>	Product		Polished Chrome	Oil Rubbed Bronze	PVD Satin Nickel	
Σ	Number	Description	002	224	295	
TRI	T440.740 <sup>*</sup>	Two-handle Thermostat Trim Kit with separate volume control.				

GH VALVE BODIES	Product Number	Description
5	R520	Rough Valve Body less trim - 1/2" NPT Inlets/Outlets
RO	R540	Rough Valve Body less trim - 3/4" NPT Inlets/Outlets

\*NOTE: When used as a Bath/Shower a separate diverter valve is required (such as R420 or R430). Requires twin ell (must be ordered separately) for use with diverter spouts.

#### \*\* ROUGH & TRIM MUST BE ORDERED SEPARATELY.