

SELECTRONIC[™] FloWise[®] EXPOSED 0.5 GPF URINAL FLUSH VALVE

HARD-WIRED AC POWERED, SENSOR OPERATED





GENERAL DESCRIPTION:

Exposed, Hardwired AC Powered, Sensor Operated Selectronic™ Urinal Flush Valve for 3/4" top spud urinals.

Inlet includes 3/4" I.P.S. angle stop with back-flow protection, vandal-resistant cap, sweat solder kit, cover tube and wall flange.

Outlet includes 3/4" vacuum breaker, spud coupling and flange.

PRODUCT FEATURES:

- Exclusive Pressure Compensation feature eliminates the need for the installer to adjust the stop valves, saving time and money and ensuring water savings
 • Electronic flush valve with Selectronic™ proximity system
- for "Hands Free" operation
- Includes UL approved hardwired AC transformer
- Input Voltage: 100 250 VAC, 50 / 60 Hz. Output Voltage: 6 VDC.
- Self-Cleaning Piston operation with integral wiper spring prevents clogging and reduces maintenance
- Piston operation delivers superior flush accuracy and repeatability
- Adjustable tailpiece
- Chemical resistant EPDM seals are unaffected by chloramines and ammonia
- Valve remains closed and does not need to be reset after loss of power or water pressure
- Stadium Feature: Valve automatically switches to water conservation mode during periods of heavy usage Fully Mechanical Manual Override Button can flush toilet
- during a power outage
- Vandal-resistant metal cover plate (for 2-gang electric box supplied by others) with no visible fasteners
- Sensor & electronic controls are fully enclosed and water
- Range can be adjusted manually or by remote control Sanitary Flush Valve automatically flushes after 24 hours of non-use to clean fixture & maintain trap seal
- No external volume adjustment
- 5 second Arming Delay prevents unintentional flushing 3-second Flush Delay
- Can be installed left or right-handed

MODEL NUMBER:

☐ 6062.051.002 HARD-WIRED AC POWERED:

Includes UL-approved Hard-Wired AC transformer (electrical box by others). 11-1/2" rough-in

☐ 6061.051.002 MULTI-AC POWERED:

Includes 10' extension cable. One transformer (sold separately) can operate up to 15 faucets and/or flush valves. 11-1/2" rough-in

OPERATING PRESSURE:

Overall Range: 20-125 psi**

Recommended: 20 psi (flowing)-80 psi (static)


FLOW REQUIREMENT:

10gpm (37.9 L/min.)

** Water pressure over 80 psi is not recommended for most plumbing fixtures.

ACCESSORIES:

• Cast wall flange (3/4")



MEETS THE AMERICANS WITH DISABILITIES ACT GUIDELINES AND ANSI A117.1 REQUIREMENTS FOR ACCESSIBLE AND USABLE BUILDING FACILITIES-CHECK LOCAL CODES

RECOMMENDED SPECIFICATION:

Electronic proximity infrared sensor activated toilet flush valve shall feature self-cleaning piston valve. Includes a UL listed hardwired power supply that provides 6 VDC power to run system. Includes a fully mechanical manual over-ride that can provide a complete flush without power. Includes cast brass valve body and metal cover with chrome finish and vandal resistant stop cap. Angle stop with back-flow protection and vacuum breaker included. 0.5 gpf / 1.9 Lpf. Flush valve shall be American Standard Model # 606_.051.002




SELECTRONIC™ FloWise® EXPOSED 0.5 GPF URINAL FLUSH VALVE

HARD-WIRED AC POWERED, SENSOR OPERATED

LISTINGS:

- ASSE 1037
- ANSI/ASME A112.19.2
- ADA Compliant



MEETS THE AMERICANS WITH DISABILITIES ACT GUIDELINES AND ANSI A117.1 REQUIREMENTS FOR ACCESSIBLE AND USABLE BUILDING FACILITIES-CHECK LOCAL CODES