

PRIOLO 16-1/2" HEIGHT 1.6 GPF FLUSHOMETER TOILET

PRIOLO 16-1/2" HEIGHT 1.6 GPF

- Floor mount rear outlet flushometer valve toilet
- Vitreous china
- Low-consumption (6.0 Lpf/1.6 gpf)
- EverClean® surface inhibits the growth of stain- and odor-causing bacteria, mold, and mildew on the surface
- 16-1/2" rim height for accessible application
- Condensation channel
- Elongated bowl
- Powerful direct-fed siphon jet action
- Fully glazed 2-1/8" trapway
- 1-1/2" inlet spud
- 2 bolt caps
- 100% factory flush tested

- ☐ **3695.016** Elongated bowl only, top spud
- ☐ **3697.016** Elongated bowl only, back spud
- ☐ **3696.016** Elongated bowl only, top spud with slotted rim for bedpan holding (White only)
- ☐ **3698.016** Elongated bowl only, back spud with slotted rim for bedpan holding (White only)

Component Parts:

- ☐ **047007-0070A** Inlet spud (furnished with bowl)
- ☐ **481310-100** Bolt caps with retainers (furnished with bowl)

Nominal Dimensions:

752 x 356 x 438mm
(29-5/8" x 14" x 17-1/4")

Recommended working pressure—between
25 psi at valve when flushing and 80 psi static

Fixture only, less seat and flush valve

Compliance Certifications -

Meets or Exceeds the Following Specifications:

- ASME A112.19.2 for Vitreous China Fixtures
- CAN/CSA International B45



SEE REVERSE FOR ROUGHING-IN DIMENSIONS

To Be Specified:


- ☐ Color: ☐ White ☐ Bone ☐ Linen
- ☐ Seat:
 - ☐ American Standard #5901.100 Heavy duty open front less cover
 - ☐ American Standard #5905.100 Extra heavy duty open front less cover
- ☐ Alternative Seat:
 - ☐ Olsonite #95 open front seat less cover
 - ☐ Church #9500C open front seat less cover
- ☐ Flushometer Valve:
 - ☐ American Standard Selectronic™ #6065.161.002 DC Power (Top Spud)
 - ☐ American Standard Selectronic™ #6065.261.007 DC Power (Back Spud)
 - ☐ American Standard Selectronic™ #6067.261.007 AC Power (Back Spud)
 - ☐ American Standard Selectronic™ #6068.261.007 Multi AC Power (Back Spud)



MEETS THE AMERICANS WITH DISABILITIES ACT GUIDELINES
AND ANSI A117.1 REQUIREMENTS FOR ACCESSIBLE AND USABLE
BUILDING FACILITIES - CHECK LOCAL CODES.


PRIOLO 16-1/2" HEIGHT 1.6 GPF FLUSHOMETER TOILET

3695.016/3696.016



DIMENSIONS (Nominal) NOTE: Distance from floor to closet flange centerline (rough-in) must be 4" (102 mm) with flange surface flush to 1/16" (1.6mm) max. beyond finished wall.

3697.016/3698.016



DIMENSIONS (Nominal) NOTE: Distance from floor to closet flange centerline (rough-in) must be 4" (102 mm) with flange surface flush to 1/16" (1.6mm) max. beyond finished wall.

NOTES:

PRODUCT 3695.160 AND 3696.160 SHOWN, 3697.160 AND 3698.160 SAME AS EXCEPT WITH SLOTTED RIM FOR BED PAN HOLDING. TO COMPLY WITH AREA CODE GOVERNING THE HEIGHT OF VACUUM BREAKER ON THE FLUSHOMETER VALVE, THE PLUMBER MUST VERIFY DIMENSIONS SHOWN FOR SUPPLY ROUGHING. FLUSHOMETER VALVE NOT INCLUDED WITH FIXTURE AND MUST BE ORDERED SEPARATELY. FLUSHOMETER VALVE REQUIREMENTS FOR 12" (305MM) ROUGH-IN: SWEAT EXTENSION NIPPLE IS REQUIRED. REFER TO VALVE MANUFACTURER AND LOCAL CODES.

IMPORTANT: Dimensions of fixtures are nominal and may vary within the range of tolerances established by ANSI Standard A112.19.2. These measurements are subject to change or cancellation. No responsibility is assumed for use of superseded or voided pages.