

Diversey

Alpha-HP® Multi-Surface Cleaner

An all-in-one, multi-purpose cleaner concentrate based on proprietary Accelerated Hydrogen Peroxide (AHP®) technology.

Environmentally Preferred

- Green Seal™ Certified

Increase Performance

- Powered by Accelerated Hydrogen Peroxide
- Blends commonly used chemicals with low levels of hydrogen peroxide for high productive cleaning

Versatile

- Use on all washable surfaces
- Multiple dilution rates
- Use as a carpet prespray or carpet extraction cleaner



Use Directions

Heavy Duty Spray-and-Wipe Cleaning or Restroom Cleaning

- Dispense using cold water into spray bottle at 1:64 dilution.
- Spray and wipe surfaces or apply product to carpet spot, agitate and rinse with water.

Glass and Medium Duty Spray-and-Wipe Cleaning

- Dispense using cold water into spray bottle at 1:128 ratio.
- Spray and wipe surfaces.

Floor Cleaning

- Use at 1:128 or 1:256 dilution.
- Dispense using cold water into bucket or autoscrubber.
- Apply to floors and allow to air dry or pick up excess water prior to opening to traffic.
- Floors will be slippery until dry.
- If applying finish or maintainer, a rinse is required.

For Carpet Prespray

- Dilute to 1:128 using cold water.
- Prespray area to be cleaned and extract with cold water.

For Carpet Extraction

- Dispense using cold water into extraction tank at 1:256.
- Extract according to carpet extractor instructions.

Wipes

- Pull wipe from canister and use to clean hard surfaces.
- Discard after use.
- Note: Floors will be slippery until dry. Allow hard surfaces to completely dry before contact. Never flush wipes into toilets. Never use wipes for personal hygiene or for infant wipes.

Product Specifications

Description	
Color/Form	Colorless liquid
Flash Point	> 200° F (> 93.4° C)
pH	1.2 (Concentrate) 2.36 (Use Dilution 1:64, Wipes)
Phosphates	0%
Scent	Citrus
Shelf Life	Complete
Solubility	1.013
Specific Gravity	8% (Concentrate) 1.9% (Wipes)

Available Items

Product Code		Description/Package Size	Dilution
93350727*		2 x 50.7 oz./1.5 L RTD*	1:64, 1:128, 1:256
3350727			
93350743*		1 x 1.32 gal./5 L RTD*	1:64, 1:128, 1:256
3350743			
3401512*		2 x 84.5 oz./2.5 L J-Fill*	1:64, 1:256
93364387		6 x 225 Count Wipes	Ready-To-Use
3364387			

*Meets Green Seal's GS-37 standard.

Safety Reminder

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use, and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDSs are available on-line at www.sealedair.com or by calling 888 352 2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate. Please refer to the Diversey HazMat Library, only available through Internet Explorer, <http://naextranet.diversey.com/dot/>, for up to date shipping information.

Green Seal® Certified mark is a registered certification mark owned by Green Seal, Inc.

GREENGUARD Indoor Air Quality Certified® is a registered certification mark of Air Quality Sciences, Inc.

WoolSafe Approved® logo is a registered certification mark owned by the WoolSafe Organization.

AHP and Design® are registered trademarks of Virox Technologies, Inc. used under license.