

Diversey

Heavy Duty Prespray



Cleans heavily soiled carpets with a unique polymer-enhanced formula that also prevents resoiling.

Effective

- Cleans tough soils in heavy traffic areas
- Carpets stay cleaner longer due to exclusive soil barriers that help resist resoiling
- pH neutral

CRI™ Certified

 Meets the specification for the Carpet and Rug Institute Seal of Approval





Heavy Duty Prespray



Use Directions

For Prespray Cleaning

- Thoroughly vacuum carpet and pre treat spots.
- Dilute 10 oz. Heavy Duty Prespray with 1 gallon hot water (1 L with 12 L) in pump-up sprayer or fill directly from J-Fill® dispenser.
- Spray carpet completely, paying particular attention to traffic lanes and spots.
- Agitate with a carpet rake, extractor brush, shampoo brush or bonnet.
- Allow 5–10 minutes for Heavy Duty Prespray to completely loosen soils.
- Thoroughly extract carpet with Extraction Rinse according to use directions. Use Liquid Defoamer in recovery tank if required.

For Bonnet Cleaning

- Dilute at 1:32 or 4 oz./gal. (35 mL per L) with warm water.
- Apply light mist onto carpet bonnet.
- Bonnet buff carpet with your pad. Flip pad when soiled. When both sides are soiled, rinse or launder.
- This solution can also be used for spot treatment. Treat spot, agitate and rinse thoroughly.

Product Specifications

Description	SC	
Color/Form	Clear yellow, liquid	
Flash Point	> 200° F (>93.4° C)	
рН	8.2 (Concentrate) 7.78 (Use Dilution 1:40)	
Scent	Floral fruity	
Shelf Life	2 years	
Solubility	Complete	
Specific Gravity	1.058	
Description	Concentrate	
Description Color/Form	Concentrate Clear yellow, liquid	
Color/Form	Clear yellow, liquid	
Color/Form Flash Point	Clear yellow, liquid > 200° F (>93.4° C) 8.0 (Concentrate)	
Color/Form Flash Point pH	Clear yellow, liquid > 200° F (>93.4° C) 8.0 (Concentrate) 7.5 (Use Dilution 1:12)	
Color/Form Flash Point pH Scent	Clear yellow, liquid > 200° F (>93.4° C) 8.0 (Concentrate) 7.5 (Use Dilution 1:12) Floral fruity	
Color/Form Flash Point pH Scent Shelf Life	Clear yellow, liquid > 200° F (>93.4° C) 8.0 (Concentrate) 7.5 (Use Dilution 1:12) Floral fruity 2 years	

Available Items

Product Co	de	Description/Package Size	Dilution
904266 04266	 -	4 x 1 gallon / 3.78 L Container	1:12, 1:32
904274 04274	== +	2 x 2.5 L / 84.5 oz. J-Fill® Bottles - SC	1:40

Safety Reminder

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use, and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDSs are available on-line at www.sealedair.com or by calling 888 352 2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate. Please refer to the Diversey HazMat Library, only available through Internet Explorer, http://naextranet.diversey.com/dot/, for up to date shipping information.

WoolSafe Approved* logo is a registered certification mark owned by the WoolSafe Organization. CRI Seal of Approval Logo is a certification mark owned by the Carpet and Rug Institute.