41 Series





Job Name:	
Job Location:	
Engineer:	
Contractor:	
Tag:	
PO#:	
Rep:	
Wholesale Dist.:	

VARRANTY ADE IN USA

DESCRIPTION

An economical way to shut-off air lines. Standard spring bottom (-01) with 5/32" port are tested at 80 psig. Optional nut bottom (-04) with 1/8" port are suitable for pressures to 200 psig. Various handle configurations available.

FEATURES

- Standard Apring Bottom (5/32" Port)
- Air Cocks Tested at 80 psi
- Optional Nut Bottom (1/8" port) Suitable to 200 psig
- Standard Satin Brass Finish
- Maximum temperature is 500° F

APPROVALS

- (-01) Standard Spring Bottom
- (-04) Nut Bottom

STANDARD MATERIALS LIST

	SERIES NUMBER	SIZE (IN.)	WT./100 (LB.)
	TEE HANDLE ROUND SHOULDER		
	41-060	1/8	12.8
No. of the second se	41-070	1/4	13.0
	1AH BET	OULDER	
	41-080	3/8	17.0
The second se	41-090	1/2	20.0
	LEVER H	ANDLE ROUND SH	OULDER
	41-120	1/8	13.1
B	41-130	1/4	14.2
	LEVER HA	ANDLE HEXAGON S	HOULDER
	41-140	3/8	17.0
	41-150	1/2	22.9
1	TEE HANDLE DOUBLE MALE THREAD		
	41-180	1/8	14.0
	41-190	1/4	17.9
	41-203	3/8	20.0
1	41-210	1/2	33.1
	LEVER HANDLE DOUBLE MALE THREAD		
	41-220	1/8	14.0
	41-230	1/4	18.5
territer and the second	41-240	3/8	19.1
	41-251	1/2	31.3
Contract (Prove)	TEE HANDLE BIBB NOSE		
	41-260	1/8	14.5
	41-270	1/4	16.3
	41-280	3/8	33.3
	41-330	1/2	36.0

	SERIES NUMBER	SIZE (IN.)	WT./100 (LB.)
	LEVER HANDLE DOUBLE FEMALE		
	41-430	1/8	14.8
	41-440	1/4	13.0
	41-450	3/8	23.0
1	41-451	1/2	27.0
	LEVER HANDLE MALE & FEMALE		
	41-460	1/8	15.2
	41-470	1/4	15.0
	41-480	3/8	23.0
1	41-481	1/2	27.0
	TEE HANDLE	MALE & FEMALE HE	EX SHOULDER
	41-490	1/8	17.0
ADDRESS OF THE OWNER	41-500	1/4	15.0
AUTOMATIC COMMENT	41-510	3/8	23.0
	41-511	1/2	25.0
=	LEVER HANDLE MALE & FEMALE HEX SHOULDER		
	41-520	1/8	14.0
	41-530	1/4	15.0
	41-540	3/8	22.1
	41-541	1/2	27.0
	TEE HANDLE DOUBLE FEMALE HEX SHOULDER		
	41-550	1/8	17.0
	41-560	1/4	17.0
	41-570	3/8	25.0
4	41-571	1/2	28.3



This specification is provided for reference only. Apollo reserves the right to change any portion of this specification without notice and without incurring obligation to make such changes to Apollo products previously or subsequently sold. Most current information available at apollovalves.com.



Valves SUBMITTAL

41 Series Air Cocks

Continued from previous page

	SERIES NUMBER	SIZE (IN.)	WT./100 (LB.)
	LEVER HANDLE BIBB NOSE		
	41-290	1/8	16.5
annual date and preserve	41-300	1/4	15.0
	41-310	3/8	32.1
*	41-320	1/2	36.0
	TEE HANDLE DOUBLE FEMALE		
	41-370	1/8	13.0
	41-380	1/4	14.0
	41-390	3/8	26.0
	41-391	1/2	27.0
	TEE HANDLE MALE & FEMALE		
	41-400	1/8	13.0
	41-410	1/4	14.0
	41-420	3/8	21.0
	41-421	1/2	26.0

	SERIES NUMBER	SIZE (IN.)	WT./100 (LB.)
	LEVER HANDLE DOUBLE FEMALE HEX SHOULDER		
	41-580	1/8	15.0
	41-590	1/4	18.2
S	41-600	3/8	24.0
8	41-601	1/2	28.8
	TEE HANDLE STRAIGHT NOSE HEX SHOULDER		
	41-630	1/8	15.7
H	41-640	1/4	15.0
	LEVER HANDLE STRAIGHT NOSE HEX SHOULDER		
	41-650	1/8	14.0
and the second s	41-660	1/4	15.0



DESCRIPTION

Heavy and extra heavy patterns for higher pressure applications.

FEATURES

- Satin Brass Finish
- Spring Bottom (-01) is Tested at 100psi
- Rated for Air Pressure up to 250 psig with Nut Version
- Extra Heavy Pattern Rated for 150 SWP -Nut Bottom Only

SERIES NUMBER	SIZE (IN.)	WT./100 (LB.)		
HEAVY PATTERN TEE HANDLE DOUBLE FEMALE				
41-102-01	1/4	28.00		
LEVER HANDLE DOUBLE FEMALE				
41-103-01	1/4	27.00		
EXTRA HEAVY PATTERN TEE HANDLE DOUBLE FEMALE				
41-200-01	1/8	32.00		
41-202-01	1/4	32.00		
TEE HANDLE DOUBLE FEMALE HEXAGON SHOULDER				
41-222-01	1/4	38.00		
TEE HANDLE MALE AND FEMALE				
41-250-01	1/4	20.00		

OPTIONS

• (-04) Nut Bottom

• (-01) Standard Spring Bottom

(704) 841-6000 apollovalves.com SS1469 © 10/18 Page 2 of 2

This specification is provided for reference only. Apollo reserves the right to change any portion of this specification without notice and without incurring obligation to make such changes to Apollo products previously or subsequently sold. Most current information available at apollovalves.com.

