

Invigoration™ 5 kW Steam Generator K-5525

Material

 Generator is constructed of insulated stainless steel, which maintains the temperature while ensuring the case is safe to the touch

Technology

- Fast-Response® technology produces a luxurious steam shower in 60 seconds
- Power Clean[™] technology offers one-touch automatic cleaning and safe maintenance
- Constant Steam produces steam at a consistent rate, which greatly minimizes temperature fluctuations.

Installation

84 cubic feet maximum volume rating for custom showering applications

Required Accessories

K- 5557 Steam Generator Control Kit

or

K- 5548-K1 DTV+ Steam Adapter Kit

Recommended Accessories

K- 5559 Small drain pan

Installed component/s: Terminal block for electrical connections, and water inlet screen.

Loose component/s: 3/8 C x F Union, 1/2 C x F Union, and 3/8 C x M Union.



Codes/Standards

UL 499 CSA C22.2 No. 64

KOHLER® Steam Generator - Three-Year Limited Warranty

See website for detailed warranty information.



KOHLER, Faucets

Invigoration™

5 kW Steam Generator K-5525


3/4" NPT Pressure Relief 3/8" NPT 3-5/16" Green LED Water Inlet (84 mm) Diagnostic Light 1-5/16" 1 (33 mm) 6-1/2" 8-3/8" (165 mm) (213 mm)2-1/8" ±(54 mm) 6" (152 mm) 18" (457 mm) (51 mm) 19-1/8" (486 mm)

Minimum required access panel is 24" (610 mm) L x 15" (381 mm) H.

Allow for a minimum of 12" (305 mm) of space around all sides of the steam generator.

Allow for the drain/spill pan.

KOHLER® drain pan (shown with support blocks) sold separately.




Required Electrical Service

One dedicated circuit required.

220-240 V, 40 A, 50/60 Hz

Technical Information

All product dimensions are nominal.



Notes

Install this product according to the installation guide.

Steam room volume for this generator is 84 cubic feet (2.4 cubic meters).

For every foot of ceiling height over 8 ft (2.4 m), use the next larger steam unit.

For optimum performance, the steam generator must be installed within 25 ft (7.62 m) of the steam head.

Recommended feed water quality should be: Hardness: 60 ppm (3.4 gpg). Total Alkalinity: 150 ppm (8.8 gpg). To ensure proper operation, the feed water supply should be tested prior to operating the steam generator. If feed water quality is not within the specified limit, contact a reputable water treatment company for treatment options.

Maximum inlet pressure is not to exceed 70 psi (483 kPa).

