

PF92305

Cast Iron Effluent Pumps



Product Features


- 1/3 HP cast iron effluent pump with tethered float
- Submersible sump/effluent pump for typical residential and commercial applications
- Comes with 10' power cord with piggyback plug
- 7.6 amps, 912 watts
- Maximum head of 25 feet
- Maximum flow rate of 60 GPM
- Permanent split capacitor motor
- 3450 RPM
- Liquid temperature range 32°-120°F
- Discharge size 1-1/2" FNPT
- Handles 5/8" solids



PF92305

Product Specifications

Performance Curve



Performance Chart

Discharge Height	0'	5'	10'	15'	20'	25'
Gallons per Minute	60	56	50	35	15	6
Gallons per Hour	3600	3360	3000	2100	900	360

Warranty and Codes

These products come complete with installation, operating care and maintenance instructions. In an effort to continually improve our products, FEI will make design changes from time to time. We reserve the right to ship newly designed products to fill any order unless we agree in writing to do otherwise. PROFLO Pumps carry the following limited warranty:

- Cast Iron & Utility Pumps – 3-year limited warranty
- Thermoplastic Sump & Utility Pumps – 1-year limited warranty
- Sewage & Effluent Pumps – 1-year limited warranty

