## **TruFLOW<sup>™</sup> Classic Manifold Assembly**

Submittal Information

#### Revision B: Jan. 30, 2009 **Project Information**


| Job Name:                      |                   |
|--------------------------------|-------------------|
| Location:                      | Part No. Ordered: |
| Engineer:                      | Date Submitted:   |
| Contractor:                    | Submitted By:     |
| Manufacturer's Representative: | Approved By:      |

### **Technical Data**

| Material                           | UNS C38500 Brass    |
|------------------------------------|---------------------|
| Manifold Body Size (I.D.)          | 11⁄2"               |
| Loop Cv (valve wide open)          | 1.9 Cv              |
| Manifold Body Threaded Connections | ISO 228-G 1¼" (R32) |
| Manifold Loop Threaded Connections | ISO 228-G ¾" (R20)  |
| Max Working Pressure               | 145 psi             |
| Max Fluid Temperature              | 220°F               |
| Max Fluid Flow Rate                | 21.0 gpm            |

#### **Product Information and Application Use**

The Uponor TruFLOW<sup>™</sup> Classic Manifold system is fully assembled and mounted on a durable bracket with an end cap on the supply manifold and an end cap with vent and drain on the return manifold. R32 unions on the inlet side of the manifolds allow connections to any manifold adapters offered by Uponor. Flow balancing is made through manifold adjustments to the balancing valve on the supply manifold.



| Description                                     | Part Number   | Α   | В  | С   | D  | Е   | Weight   |
|---|---|---|--|---|--|---|--|
| TruFLOW Classic Manifold Assembly, B&I, 2-loop  | A2610200  | 1.94"   | 3.46"  | 8.25"   | 12.60"   | 8.40"   | 9.0 lbs  |
| TruFLOW Classic Manifold Assembly, B&I, 3 Loop  | A2610300  | 1.94"   | 3.46"  | 8.25"   | 12.60"   | 10.34   | 11.4 lbs   |
| TruFLOW Classic Manifold Assembly, B&I , 4 Loop | A2610400  | 1.94"   | 3.46"  | 8.25"   | 12.60"   | 12.28"  | 13.0 lbs   |
| TruFLOW Classic Manifold Assembly, B&I , 5 Loop | A2610500  | 1.94"   | 3.46"  | 8.25"   | 12.60"   | 14.22"  | 16.0 lbs   |
| TruFLOW Classic Manifold Assembly, B&I , 6 Loop | A2610600  | 1.94"   | 3.46"  | 8.25"   | 12.60"   | 16.16"  | 18.5 lbs   |
| TruFLOW Classic Manifold Assembly, B&I , 7 Loop | A2610700  | 1.94"   | 3.46"  | 8.25"   | 12.60"   | 18.10"  | 20.5 lbs   |
| TruFLOW Classic Manifold Assembly, B&I , 8 Loop | A2610800  | 1.94"   | 3.46"  | 8.25"   | 12.60"   | 20.04"  | 22.5 lbs   |
| TruFLOW Classic Manifold Assembly, B&I, 10 Loop | A2611000  | 1.94"   | 3.46"  | 8.25"   | 12.60"   | 23.92"  | 27.0 lbs   |
| TruFLOW Classic Manifold Assembly, B&I, 12 Loop | A2611200  | 1.94"   | 3.46"  | 8.25"   | 12.60"   | 27.80"  | 31.5 lbs   |
|   | TruFLOW Classic Manifold Assembly, B&I, 2-loop<br>TruFLOW Classic Manifold Assembly, B&I, 3 Loop<br>TruFLOW Classic Manifold Assembly, B&I, 4 Loop<br>TruFLOW Classic Manifold Assembly, B&I, 5 Loop<br>TruFLOW Classic Manifold Assembly, B&I, 6 Loop<br>TruFLOW Classic Manifold Assembly, B&I, 7 Loop<br>TruFLOW Classic Manifold Assembly, B&I, 8 Loop<br>TruFLOW Classic Manifold Assembly, B&I, 10 Loop | TruFLOW Classic Manifold Assembly, B&I, 2-loopA2610200TruFLOW Classic Manifold Assembly, B&I , 3 LoopA2610300TruFLOW Classic Manifold Assembly, B&I , 4 LoopA2610400TruFLOW Classic Manifold Assembly, B&I , 5 LoopA2610500TruFLOW Classic Manifold Assembly, B&I , 6 LoopA2610600TruFLOW Classic Manifold Assembly, B&I , 7 LoopA2610700TruFLOW Classic Manifold Assembly, B&I , 7 LoopA2610700TruFLOW Classic Manifold Assembly, B&I , 8 LoopA2610800TruFLOW Classic Manifold Assembly, B&I , 10 LoopA2611000 | TruFLOW Classic Manifold Assembly, B&I, 2-loopA26102001.94"TruFLOW Classic Manifold Assembly, B&I, 3 LoopA26103001.94"TruFLOW Classic Manifold Assembly, B&I, 4 LoopA26104001.94"TruFLOW Classic Manifold Assembly, B&I, 5 LoopA26105001.94"TruFLOW Classic Manifold Assembly, B&I, 5 LoopA26106001.94"TruFLOW Classic Manifold Assembly, B&I, 6 LoopA26106001.94"TruFLOW Classic Manifold Assembly, B&I, 7 LoopA26107001.94"TruFLOW Classic Manifold Assembly, B&I, 8 LoopA26108001.94"TruFLOW Classic Manifold Assembly, B&I, 10 LoopA26110001.94" | TruFLOW Classic Manifold Assembly, B&I, 2-loopA26102001.94"3.46"TruFLOW Classic Manifold Assembly, B&I , 3 LoopA26103001.94"3.46"TruFLOW Classic Manifold Assembly, B&I , 4 LoopA26104001.94"3.46"TruFLOW Classic Manifold Assembly, B&I , 5 LoopA26105001.94"3.46"TruFLOW Classic Manifold Assembly, B&I , 6 LoopA26106001.94"3.46"TruFLOW Classic Manifold Assembly, B&I , 6 LoopA26106001.94"3.46"TruFLOW Classic Manifold Assembly, B&I , 7 LoopA26107001.94"3.46"TruFLOW Classic Manifold Assembly, B&I , 8 LoopA26108001.94"3.46"TruFLOW Classic Manifold Assembly, B&I , 10 LoopA26110001.94"3.46" | TruFLOW Classic Manifold Assembly, B&I, 2-loop A2610200 1.94" 3.46" 8.25"   TruFLOW Classic Manifold Assembly, B&I , 3 Loop A2610300 1.94" 3.46" 8.25"   TruFLOW Classic Manifold Assembly, B&I , 4 Loop A2610400 1.94" 3.46" 8.25"   TruFLOW Classic Manifold Assembly, B&I , 4 Loop A2610500 1.94" 3.46" 8.25"   TruFLOW Classic Manifold Assembly, B&I , 5 Loop A2610500 1.94" 3.46" 8.25"   TruFLOW Classic Manifold Assembly, B&I , 6 Loop A2610600 1.94" 3.46" 8.25"   TruFLOW Classic Manifold Assembly, B&I , 7 Loop A2610700 1.94" 3.46" 8.25"   TruFLOW Classic Manifold Assembly, B&I , 8 Loop A2610800 1.94" 3.46" 8.25"   TruFLOW Classic Manifold Assembly, B&I , 10 Loop A2611000 1.94" 3.46" 8.25" | TruFLOW Classic Manifold Assembly, B&I, 2-loop A2610200 1.94" 3.46" 8.25" 12.60"   TruFLOW Classic Manifold Assembly, B&I , 3 Loop A2610300 1.94" 3.46" 8.25" 12.60"   TruFLOW Classic Manifold Assembly, B&I , 4 Loop A2610400 1.94" 3.46" 8.25" 12.60"   TruFLOW Classic Manifold Assembly, B&I , 4 Loop A2610500 1.94" 3.46" 8.25" 12.60"   TruFLOW Classic Manifold Assembly, B&I , 5 Loop A2610500 1.94" 3.46" 8.25" 12.60"   TruFLOW Classic Manifold Assembly, B&I , 6 Loop A2610600 1.94" 3.46" 8.25" 12.60"   TruFLOW Classic Manifold Assembly, B&I , 7 Loop A2610700 1.94" 3.46" 8.25" 12.60"   TruFLOW Classic Manifold Assembly, B&I , 7 Loop A2610700 1.94" 3.46" 8.25" 12.60"   TruFLOW Classic Manifold Assembly, B&I , 8 Loop A2610800 1.94" 3.46" 8.25" 12.60"   TruFLOW Classic Manifold Assembly, B&I , 10 Loop A2611000 1.94" 3.46" 8.25" 12.60" | TruFLOW Classic Manifold Assembly, B&I, 2-loopA26102001.94"3.46"8.25"12.60"8.40"TruFLOW Classic Manifold Assembly, B&I , 3 LoopA26103001.94"3.46"8.25"12.60"10.34TruFLOW Classic Manifold Assembly, B&I , 4 LoopA26104001.94"3.46"8.25"12.60"12.28"TruFLOW Classic Manifold Assembly, B&I , 5 LoopA26105001.94"3.46"8.25"12.60"14.22"TruFLOW Classic Manifold Assembly, B&I , 6 LoopA26106001.94"3.46"8.25"12.60"16.16"TruFLOW Classic Manifold Assembly, B&I , 7 LoopA26107001.94"3.46"8.25"12.60"18.10"TruFLOW Classic Manifold Assembly, B&I , 8 LoopA26108001.94"3.46"8.25"12.60"20.04"TruFLOW Classic Manifold Assembly, B&I , 10 LoopA26110001.94"3.46"8.25"12.60"20.92" |

#### Installation

TruFLOW Classic manifolds come fully assembled ready for installation right out of the box. The TruFLOW balancing Hex Key is used on the internal balancing valves of the supply manifold. Manifold is shipped with the appropriate number of actuator adapters (A2630028)

| Standards   | Codes                   | Listings  |  |  |  |
|---|-------------------------|---|--|--|--|
| ASTM F877   | IMC; UMC; NBC of Canada | ESR-1529; NSF-RFH   |  |  |  |
| TruFLOW Manifold Accessories  |                         |   |  |  |  |
| TruFLOW Loop Thermometer - A2610020<br>TruFLOW Manifold S&R Ball Valves- A2631250<br>TruFLOW Manifold Extension Kit- A2610100     | )                       | Thermal Actuator - A3010522<br>TruFLOW Classic Manifold Bracket - A2620006                                |  |  |  |
| Related Applications  |                         | Contact Information   |  |  |  |
| Radiant Heating and Cooling Systems<br>Snow and Ice Melting Systems<br>Permafrost Protection Systems<br>Turf Conditioning Systems |                         | Uponor, Inc.<br>5925 148 <sup>th</sup> Street West<br>Apple Valley, MN 55124 USA<br>Phone: (800) 321-4739 | Uponor Ltd.<br>2000 Argentia Rd., Plaza 1, Ste. 200<br>Mississauga, ON L5N 1W1 CANADA<br>Phone: (888) 994-7726 |  |  |

Fax: (952) 891-2008

www.uponor-usa.com

Phone: (888) 994-7726 Fax: (800) 638-9517 www.uponor.ca

# uponor