

MANIFOLD - ASTM F1807 PEX CRIMP

672 SERIES

PowerPEX™

SPECIFICATION

Sioux Chief ASTM F1807 manifolds shall be used in plumbing systems for safe distribution of hot or cold water. Manifolds shall be used in new construction or remodel applications. Manifolds can be utilized in various layouts and shall provide appropriate water distribution to supply fixtures through 3/4" or 1" trunk lines. F1807 manifolds shall be offered with or without valves and in various outlet multiples. Trunk lines can be formed to provide sweat connections, spun reduced, spun closed, or provided with F1807 inlets/outlets. Each manifold shall be assembled with no lead solder or braze and tested by Sioux Chief prior to shipment.

MATERIALS

Trunk: Copper

End Outlet: Copper or C69300* Brass

Branch: Copper or C69300* Brass

Solder: No Lead

*693 brass used in brazed configurations

APPLICATIONS

For use with hot and cold water distribution systems.

OPERATING TEMPERATURE/PRESSURE


35°F - 140°F / 20 psi - 60 psi

CERTIFICATIONS

complies with NSF 14 and 61.



Item # Submitted _____
Job Name _____
Location _____
Engineer _____
Contractor _____
PO# _____ TAG _____



672X0490



672X0699



672XV0590

Create Item Number

672 ABC

e.g. 672X0490 = 1" L copper trunk, 4 1/2" ASTM F1807 no lead branches, 3/4" PEX inlet x spun closed
Additional options available at www.siouxchief.com

- | | | |
|---|--|---|
| A Manifold Type | B Branch multiples | C Trunk type |
| <input type="checkbox"/> X F1807 branch NL(No Lead) | <input type="checkbox"/> 02 2 branches | <input type="checkbox"/> 90 1" L, 3/4" PEX x Spun Closed |
| <input type="checkbox"/> XV F1807 branch & Valve | <input type="checkbox"/> 03 3 branches | <input type="checkbox"/> 99 1" L, 3/4" PEX x 3/4" PEX |
| <input type="checkbox"/> XGV F1807 NL branch & Valve | <input type="checkbox"/> 04 4 branches | <input type="checkbox"/> 77 1" L, 1" PEX x 1" PEX |
| <input type="checkbox"/> C Compression PEX | <input type="checkbox"/> 06 6 branches | <input type="checkbox"/> 70 1" L, 1" PEX x Spun Closed |
| <input type="checkbox"/> CV Comp. PEX valve | <input type="checkbox"/> 08 8 branches | <input type="checkbox"/> 30 1" L, 3/4" Male Sweat x Spun Closed |
| <input type="checkbox"/> CB Comp. PEX balancing valve | <input type="checkbox"/> 10 10 branches | <input type="checkbox"/> 40 1" L, 1" Male Sweat x Spun Closed |
| <input type="checkbox"/> BXT Slab Manifold/Multi-port tee | <input type="checkbox"/> 12 12 branches | <input type="checkbox"/> 97 1" L, 3/4" PEX x 1" PEX |
| | <input type="checkbox"/> 13 13 branches, etc | <input type="checkbox"/> 44 1" L, 1" Male Sweat x 1" Male Sweat |
| | | <input type="checkbox"/> 10 1" L, 1" Female Sweat x Spun Closed |